

WEG BETUMINOSO 712

PRODUCT DESCRIPTION: High-build single-component bituminous coating. It is certified for contact with drinking water.

RECOMMENDED USES: Internal painting of drinking water tanks, internal structure under coating and in cofferdams, chain locker, etc. Recommended for maintenance and new works.

CERTIFICATIONS AND APPROVAL: It complies with the requirements of Anvisa Resolution No. 105 for contact with non-acid aqueous foods (drinking water).

PACKAGING:	Component	Content	Package	Unit of measurement
	Monocomponent	3,6 20	3,6 20	L

CHARACTERISTICS: **Color:** Black
Gloss: Matte
Volume solid: 51 ± 2% (ISO 3233).

Expiry Date: 12 months at 25°C.

Thickness per coat (dry): 90 µm –110 µm
Theoretical coverage: 5,1 m²/l without dilution in the thickness of 100 µm dry. Without considering the loss factors in the application.

Drying:

	10°C	25°C	35°C
Touch:	18 hours	8 hours	6 hours
Handling:	72 hours	48 hours	48 hours
Final:	-	168 hours	168 hours

Repainting Drying:

	10°C	25°C	35°C
Min	18 hours	8 hours	8 hours
Max			

SURFACE PREPARATION The performance of this product is related to the degree of surface preparation.

The surface must be clean, dry and free of any contaminants. Completely remove oils, greases and fats, as described in the SSPC-SP 1 standard.

The accumulated dirt must be removed using a dry brush, clean and dry cloth, compressed air blow, vacuum cleaner and/or with the combination of such items, and the soluble salts must be removed through wash with a great quantity of fresh water, preferably with low pressure (up to 5,000 psi) according to SSPC-SP 12/NACE No. 5.

Surface treatment through Abrasive Blasting process

Execute the abrasive blasting to near white metal, Sa 2 ½ grade of the ISO 8501-1 visual standard (A Sa 2 ½, B Sa 2 ½, C Sa 2 ½ and D Sa 2 ½) or according to SSPC-SP 10/NACE No. 2, SSPC-VIS 1 visual standard (A SP 10, B SP 10, C SP 10, D SP 10, G1 SP 10, G2 SP 10, G3 SP 10).

It is recommended a roughness profile between 40 and 85 µm.

Inspect the newly blasted surface observing the presence of surface flaws that could become apparent after this stage, adopting appropriate actions to mitigate such defects through grinding, weld filling and/or epoxy putty.

In case of oxidation on the substrate from the end of the abrasive blasting to the beginning of the coating application, the surface must be blasted again until reaching the specified visual standard.

For areas close to sea air, it is necessary to wash the surface with fresh water at low pressure (minimum 3,000 psi) before the abrasive blasting. And in some cases it is necessary to repeat the washing procedure after the abrasive blasting to remove possible soluble contaminants settled on the surface proceeding with a new abrasive blasting.

The maximum content of soluble impurities on the blasted surface according to the test described in ISO 8502-6 and distilled water must not exceed a measured conductivity according to ISO 8502-9 corresponding to a maximum content of 20 mg/cm² (2 µg/cm²) in immersed or buried areas.

Treatment of Steel Carbon Surfaces

Hard superficial layers (for example, layers resulting from flame cut) must be removed by grinding it before beginning the abrasive blasting.

All the welds must be inspected e, if necessary, be repaired before the ending of the abrasive blasting. Porosity, cavities, weld splashes, etc. must be repaired by means of proper mechanical treatment or weld repair; in the other areas, round the sharp edges ($r \geq 2$ mm, ISO 8501-3).

For further information, consult WEG Technical Department.

PREPARATION FOR APPLICATION

Mixture

Homogenize the contents of the package by means of mechanical or pneumatic stirring. Ensure that no sediment is settled at the bottom of the package.

Diluent

Alkydic diluent 1024

Dilution

Depending on the application method, dilute at most 5%

Do not dilute with solvents that are not allowed by local legislation and do not exceed the recommended dilution percentage.

The quantity of diluent may vary depending on the type of equipment used and the ambient conditions during the application.

Excessive dilution of the coating may affect the formation of the film and appearance and hinder the attainment of the specified thickness.

Pot life of the mixture (25°C)

Not relevant

APPLICATION FORMS

The data below is a guide, and similar equipment may be used.

In the spray application, make a 50% overlap in each gun pass, concluding with a cross pass. This technique is used to avoid uncovered and unprotected areas and to obtain a suitable aesthetic finish.

Reinforce all sharp edges, cracks and weld beads with a brush to prevent premature failures in these areas.

Changes in nozzle sizes and pressures may be necessary to improve the spraying characteristics.

Before the application, make sure the equipment and its components are clean and in the best condition.

Purge the compressed air line to prevent contamination of the coating.

The data below is a guide, and similar equipment may be used.

Airless Gun:

Use Airless:	Use at least pump 60: 1
Fluid pressure:	2000 – 3000 psi
Hose:	3/8" internal diameter

Nozzle:	0,017" - 0,025"
Dilution:	Max. 5%

Brush:

Only recommended for retouching small areas or strip coat (screws, nuts, weld beads, sharp edges and retouching). Use a brush 75 to 100 mm wide for larger surfaces and 25 to 38 mm for retouching.

Roller:

Only recommended for small areas or retouching. Use a thin nap, seamless sheepskin or microfiber roller for epoxy coatings.

Not recommended for painting the interior of tanks

For application with brush and/or roller, application in two or more passes may be necessary to obtain a uniform layer according to the recommended film thickness per coat.

Cleaning the equipment:

Alkydic diluent 1024

NOTE:

Clean all equipment immediately after use.

Do not leave material in the hoses, spray guns and equipment used in the spraying. Thoroughly wash all equipment used.

Furthermore, it is a good working practice to periodically wash the spray equipment along the day. The cleaning frequency will depend on the amount sprayed, temperature and elapsed time, including all delays.

PERFORMANCE IN THE APPLICATION

For a good performance of the product, we recommend following the directions below:

Minor variations in color, appearance and gloss (more noticeable in dark colors) may occur, as well as delay in curing and impairment of surface performance, when applied during periods of high air relative humidity, rainy days, low temperatures or in case the coated parts are put to dry outdoors.

In paintings executed on the seafront, if exposed to the action of sea air, we recommend to wash with fresh water between coats eliminating the settled impurities.

It should not be applied in adverse conditions, such as air relative humidity above 85% or on condensed surfaces. Small variations in color, appearance and gloss of the coated parts may occur in periods of high air relative humidity, rainy days, at low temperatures or in situations where the coated parts are placed to dry outdoors.

In cases where the product will be used to paint the interior of drinking water tanks, we recommend to wait seven days to start filling the tank.

We recommend coating only if the measured surface temperature is at least 3 °C above the dew point temperature.

For better application properties, the coating temperature should be between 21 - 27 °C prior to the mixing and application.

In coatings with variation in the application method in the same job, the final appearance and gloss of the painted surfaces may present differences.

The temperature of the substrate, the weather and environmental conditions during the application and during the curing of the product, and the thickness of the applied film may interfere with the product drying time.

For a good performance of the product, we recommend following the directions below:

For further information, consult WEG Technical Department.

SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals.

Please read carefully all the information contained in the MSDS of this product, available at: www.weg.net.

Store in a covered, well-ventilated area. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists / vapors / aerosols generated during handling and / or application.

Wear protective gloves / protective clothing / eye protection / face protection.

Avoid release of the product and its packaging, as well as materials used during handling and application in the environment.

NOTE:

The information contained in this technical datasheet is based upon the experience and knowledge acquired in the field by the technical team of WEG.

If using the product without prior inquiry to WEG Coating concerning its suitability for the customer's intended purpose, the customer is aware that the use shall be its exclusive responsibility, WEG not being

responsible for the behavior, safety, suitability or durability of the product.

Certain information contained in this datasheet is merely an estimate, and can undergo variances arising from factors outside the manufacturer's control. Thus, WEG does not guarantee and does not assume any responsibility regarding the yield, performance or any other material or personal damage resulting from the incorrect use of the products concerned or the information contained in this Technical datasheet.

The information contained in this technical datasheet is subject to periodic modification, without prior notice, due to the policy of evolution and continuous improvement of our products and services, providing solutions with quality to satisfy our customers' requirements.

