

W-TERM HPA 660

PRODUCT DESCRIPTION

Single-component modified silicone-based finish paint, heat-resistant up to 600°C. Can be applied directly over carbon steel, aluminum alloy metallization, or W-TERM CVD 660 primer.

RECOMMENDED USE

Indicated for painting exhausts, chimneys, furnaces, boilers, heat exchangers, pipes, or other equipment operating at temperatures of:
 150-350°C - continuous period;
 350-500°C - up to 24 hours;
 500-600°C - up to 1 hour.

CERTIFICATIONS AND APPROVALS

When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.

PACKAGING

Single Component	3.6L Package containing 3.6L 20L Package containing 20L
-------------------------	--

CHARACTERISTICS

Color	Black.
Gloss	Matte
VOC content	832.59 g/l
Volume Solids	50 ± 2% (ISO 3233)
Shelf Life	12 months
Dry Film Thickness	20 µm - 25 µm
Dry Heat Resistance	Maximum temperature: 600 °C. The product maintains its physical and chemical properties up to 600 °C.
Theoretical Coverage	22,22 m ² /l without dilution at a dry film thickness of 23 µm. Loss factors during application are not considered.

DRYING

Drying	25 °C
Manipulation	30 min

SURFACE PREPARATION

Standard Surface Preparation

The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

Degreasing

Completely remove oils and greases by applying a degreasing product or according to the solvent cleaning method. Whenever cleaning surfaces with cloths, replace them to avoid saturation. Do not use cotton waste or colored cloths.

Over Aged Coating

Application over aged paint is allowed only if it is temperature-resistant and adhered to the substrate. Manual/mechanical sanding is recommended for better adhesion, followed by cleaning the dust generated.

Primer must be clean, dry, and free of contaminants. The topcoat must be applied within the primer recoat interval. Consult the primer technical bulletin for correct application.

The product must be applied over Zinc Ethyl Silicate N 1661 or Zinc and Aluminum Ethyl Silicate N



2231 to form a coating system with anticorrosive protection and high-temperature resistance. For proper application, refer to the primer technical data sheet.

APPLICATION PREPARATION

Mixing	Homogenize the content of the container using mechanical or pneumatic stirring. Ensure no sediment remains at the bottom of the container.
Thinner	ALKYDIC DILUENT 1024
Dilution	Depending on the application method, dilute to a maximum of 15%.
Notes	The amount of Diluent may vary depending on the type of equipment used and environmental conditions during application. Only add Diluent after complete mixing of the other components. Do not dilute with solvents not allowed by local legislation, and do not exceed the indicated dilution percentage. Excessive dilution may affect film formation, appearance, and make it difficult to achieve the specified thickness.
Pot Life	Not relevant.

APPLICATION METHODS

Conventional Spray Gun	Spray gun: JGA 502/3 Devilbiss or equivalent Fluid nozzle: EX Air cap: 704 Atomization pressure: 60 - 65 psi Tank pressure: 10 - 20 psi.
Roller	Use a short-haired, seamless wool or synthetic roller for epoxy paints. Recommended only for small areas or touch-ups. Use a low-pile seamless wool roller or synthetic roller for epoxy paints. For application with brush and/or roller, it may be necessary to apply two or more coats to achieve a uniform layer and the recommended film thickness.
Brush	Recommended only for small area touch-ups or "stripe coat" (screws, nuts, weld beads, sharp corners, and touch-ups). Use a brush 75 to 100 mm wide for larger surfaces and 25 to 38 mm for touch-ups.
Cleaning of the equipments:	ALKYDIC DILUENT 1024
Notes	The data presented serves as a guide and similar equipment may be used. Changes in pressures and nozzle sizes may be necessary to improve spraying characteristics. Purge the compressed air line to avoid paint contamination. Before application, ensure that the equipment and respective components are clean and in optimal condition. After mixing two-component products, if there are application stops and the pot life has been exceeded (paint shows variation in flow), it can no longer be re-thinned for later application. Reinforce all sharp corners, gaps, and weld beads with a brush to avoid premature failures in these areas. Do not leave material in hoses, guns, or equipment used for spraying. Thoroughly wash all used equipment.

APPLICATION PERFORMANCE

The adhesion test can only be carried out after full curing of the film.

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

For optimal application properties, the paint temperature should be between 21°C and 27°C before mixing and application.



Painting is recommended only if surface temperature is at least 3°C above the dew point.

Substrate temperature, climatic and environmental conditions during application and curing, as well as applied film thickness, may affect drying time.

Full cure is achieved when the equipment is put into operation, reaching a temperature above 150°C.

The maximum product performance is obtained when the painted equipment is put into operation at a temperature of 180°C to 230°C. It is recommended to slightly raise this temperature.

Must not be applied under adverse conditions, such as relative humidity (RH) above 85%, as color and appearance changes may occur.

For equipment operating below 150°C, a pre-cure of 30 minutes at 180°C is required.

Discoloration may occur when subjected to high temperature.

Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

Repainting is not recommended; only touch-up where necessary.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: www.weg.net.

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.

Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.

Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.

The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.
