

POLITHERM 55 HB R SM BLACK W RAL 9005 BR

PRODUCT: 16212515

DESCRIPTION / USES: Epoxy powder coating for indoor use on metallic parts.

CHARACTERISTICS:

Resin:	Epoxy
Specific gravity:	1,36 ± 0,10 g/cm ³
Stability:	6 months (máx. 30°C)
Observations:	Free of heavy metals and other substances provided for in Directive 2015/863 EU of 03/31/2015 (RoHS).

APPLICATION CHARACTERISTICS:

Surface:	Ferrous and non-ferrous
Surface preparation:	Ferrous: Phosphatization Non-ferrous: Chromatization or phosphatization*
Cure conditions:	10 minutes at 140 °C**
Thickness:	100 – 120 µm
Application system:	Electrostatic gun

AFTER CURE CHARACTERISTICS*:**

TEST	METHOD	SPECIFICATION
ADHESION	ASTM D 3359	: GR0
GLOSS @ 60°	ASTM D 523	: Minimum 80 UB
IMPACT (REVERSE)	ASTM 2794	: Minimum 40 kg X cm
FLEXIBILITY (CONIC MANDREL)	ASTM D 790 / ISO 178	: Maximum 5 mm

CHEMICAL RESISTANCE ***

Salt spray:	: Minimum 500 h (ASTM B117 – 03)
Humidity:	: Minimum 1000 h (35°C)

* For non-ferrous metals phosphatizing, please contact our technical service.

** After stabilization on correct temperature (metal temperature).

*** The tests were conducted on degreased steel panels in accordance with the cure and thickness specifications. The figures may be change, depending on the surface characteristics. For chemical resistance tests the panels were degreased and treated with tricationic phosphat.

IMPORTANT: If is not possible the use of the product according to the directions given above we ask you to contact our technical service.

This product is not suitable for parts intended to be glued using silicon glue.

STORAGE: Fresh, dry and covered place.