



W-TERM CVA 660 ALUMINUM

PRODUCT DESCRIPTION		Single-component modified silicone-based finish paint, heat-resistant up to 600°C. Can be applied directly over carbon steel, aluminum alloy metallization, or W-TERM CVD 660 primer.
RECOMMENDED USE		Indicated for painting exhausts, chimneys, furnaces, boilers, heat exchangers, pipes, or other equipment operating at temperatures of: 150-350°C - continuous period; 350-500°C - up to 24 hours; 500-600°C - up to 1 hour.
CERTIFICATIONS AND APPROVALS		When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.
PACKAGING	Single Component	3.6L Package containing 3.6L 20L Package containing 20L
CHARACTERISTICS	Color	Aluminum. Colors.
	Gloss	Semi-Matte
	VOC content	773.44 g/l
	VOC content	6.0 (lb/gal). Note: The average of VOC on the line can vary depending on the color.
	Volume Solids	30 ± 5% (ISO 3233)
	Shelf Life	12 months
	Dry Film Thickness	0.8 mils (20 µm) - 1.2 mils (30 µm)
	Dry Heat Resistance	Maximum temperature 1112 °F (600 °C). The product maintains its chemical properties up to a temperature of 1112 °F (600 °C), but from 150°C, color and gloss variations in the paint may occur.
	Theoretical Coverage	611.3 ft²/ga (15,00 m2/l) without dilution at a dry film thickness of 0.8 mils (20 µm). Loss factors during application are not considered.
DRYING	Drying	25 °C 40 min
	Oven Drying	180 °C 30 min
SURFACE PREPARATION		Standard Surface Preparation The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department. Remove accumulated dirt using a dry brush, clean dry cloth, compressed air blow, vacuum, or a combination of these. Remove soluble salts by washing with plenty of fresh water, preferably under low pressure (up to 5,000 psi), according to SSPC-SP12/NACE No. 5 standard.

Degreasing

Completely remove oils and greases by applying a degreasing product or according to the solvent cleaning method. Whenever cleaning surfaces with cloths, replace them to avoid saturation. Do not use cotton waste or colored cloths.

APPLICATION PREPARATION

Mixing	Homogenize the content of the container using mechanical or pneumatic stirring. Ensure no sediment remains at the bottom of the container.
Thinner	Not applicable.
Dilution	Ready to use.
Notes	No dilution is required. Product ready to use. If necessary, consult the WEG Technical Department.
Pot Life	Not relevant.

APPLICATION METHODS

Conventional Spray Gun	Spray gun: JGA 502/3 Devilbiss or equivalent Fluid nozzle: EX Air cap: 704 Atomization pressure: 60 - 65 psi Tank pressure: 10 - 20 psi.
Brush	Recommended only for small area touch-ups or "stripe coat" (screws, nuts, weld beads, sharp corners, and touch-ups).
Notes	The data presented serves as a guide and similar equipment may be used. Changes in pressures and nozzle sizes may be necessary to improve spraying characteristics. Purge the compressed air line to avoid paint contamination. Before application, ensure that the equipment and respective components are clean and in optimal condition. Reinforce all sharp corners, gaps, and weld beads with a brush to avoid premature failures in these areas. Do not leave material in hoses, guns, or equipment used for spraying. Thoroughly wash all used equipment.

APPLICATION PERFORMANCE

An increase in viscosity of this material may occur during storage, being a normal characteristic of the product.

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

For optimal application properties, the paint temperature should be between 21°C and 27°C before mixing and application.

Painting is recommended only if surface temperature is at least 3°C above the dew point.

Substrate temperature, climatic and environmental conditions during application and curing, as well as applied film thickness, may affect drying time.

Do not apply under adverse conditions, such as RH above 85%, as gloss and color may slightly change. Do not apply on condensed surfaces.

For equipment operating below 150°C, a pre-cure of 30 minutes at 180°C is required.

Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read



all information contained in the SDS of this product, available at: www.weg.net.
 Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.
 Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.
 Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.
 Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.
 In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.
 Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.
 The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.