



W-FENOXI HBD 36

PRODUCT DESCRIPTION

Two-component modified novolac epoxy primer, amine-cured, Low VOC, and high-build, providing excellent edge protection compared to conventional epoxies.

RECOMMENDED USE

Suitable for highly aggressive environments, providing excellent anticorrosive protection on steel. Developed for application in storage tanks for petroleum products, chemicals, freshwater, seawater, and maritime/offshore structures. It can also be used on decks, oil and natural gas exploration platforms, onboard machinery, pipelines, etc. It is particularly recommended for environments where chemical resistance, abrasion, and impact are essential requirements.

CERTIFICATIONS AND APPROVALS

When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.

This product complies with Ministry of Health Ordinance GM/MS No. 888, dated May 4, 2021.

PACKAGING

Component A	0.95 US gal Package containing 0.76 US gal
Component B	0.24 US gal Package containing 0.19 US gal

CHARACTERISTICS

Color	White.
Gloss	Gloss
VOC content	0.03 lb/gal
Volume Solids	98 ± 2% (ISO 3233)
Shelf Life	12 months
Dry Film Thickness	17.7 mils - 21.7 mils
Dry Heat Resistance	Maximum temperature 248 °F. The product maintains its chemical properties up to a temperature of 248 °F, but from 140°F, color and gloss variations in the paint may occur.
Theoretical Coverage	79.9 ft ² /gal without dilution at a dry film thickness of 19.7 mils. Loss factors during application are not considered.

DRYING

Drying	50 °F 77 °F 95 °F		
	Touch	12 hours	5 hours
Manipulation	48 hours	14 hours	8 hours
Final	10 days	4 days	24 hours
Recoat Drying	50 °F 77 °F 95 °F		
	Minimum	48 hours	14 hours
Maximum	21 days	12 hours	10 days

SURFACE PREPARATION

Standard Surface Preparation

The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

The surface must be clean, dry, and free of contaminants. Completely remove oils, greases, and fats according to SSPC-SP1.

Accumulated dirt must be removed using a dry brush, and soluble salts must be removed by washing with fresh water under high pressure.



Recommended Surface Profile

It is recommended a roughness profile between 1.57 and 3.35 mils.

Abrasive Blasting

For other applications, it is recommended to paint on surfaces blasted to Sa 2½ or Sa 3 grade, according to SSPC-SP10 or SSPC-SP5, respectively. Visual standard ISO 8501-1.

If oxidation occurs between the end of abrasive blasting and coating application, the surface must be blasted again until the specified visual standard is achieved.

Over Primer

Epoxy primer: over firmly adhered epoxy paints, adhesion by pull-off will be lower than application over standard abrasive blasting.

Existing shop primer must be removed via abrasive blasting to near-white metal, grade Sa 2½, ISO 8501-1 standard or SSPC-SP 10/NACE No.2, unless the manufacturer ensures integrity and performance of the painting system over the primer.

Respect the product recoat interval. If exceeded, perform light manual/mechanical sanding to break gloss and clean dust/residues for better adhesion between coats.

APPLICATION PREPARATION

Mixing	Homogenize the content of each component using mechanical or pneumatic stirring (A and B). Ensure no sediment remains at the bottom of the container. Add component B to component A in the indicated mixing ratio under stirring until completely homogenized, respecting the mixing ratio.
Mixing Ratio	By volume: 4 A x 1 B.
Thinner	EPOXY DILUENT 3005
Dilution	Depending on the application method, dilute to a maximum of 10%.
Pot Life	1 h 30 min The shelf life of the mixture is reduced as the ambient temperature increases. The pot-life test of the mixture is carried out according to ABNT NBR 15742; however, different volumes of paint prepared at once, combined with varying ambient and paint temperatures, will affect the mixture's shelf life, potentially resulting in outcomes different from those stated in this technical bulletin.
Induction Time	No induction time required. In very hot locations, we recommend consulting WEG's Technical Department.

APPLICATION METHODS

Airless Spray Gun	Airless: Use minimum pump 68:1 Fluid pressure: 5500 - 6000 psi Hose: 3/8" inner diameter Nozzle: 0.017- 0.025" Note: Fluid hose diameter must not be less than 1/2" with 3/8" on the whip, and its length must not exceed 16.4 ft.
Roller	Use a short-haired, seamless wool or synthetic roller for epoxy paints.
Brush	Recommended only for small area touch-ups or "stripe coat" (screws, nuts, weld beads, sharp corners, and touch-ups).
Cleaning of the equipments:	EPOXY DILUENT 3005
Notes	Changes in pressures and nozzle sizes may be necessary to improve spraying characteristics. Purge the compressed air line to avoid paint contamination.



Do not allow catalyzed product to remain in contact with application equipment, as at temperatures above the indicated "pot life", the paint will show variation in flow and will harden, making cleaning difficult.

Before application, ensure that the equipment and respective components are clean and in optimal condition.

After mixing two-component products, if there are application stops and the pot life has been exceeded (paint shows variation in flow), it can no longer be re-thinned for later application.

Reinforce all sharp corners, gaps, and weld beads with a brush to avoid premature failures in these areas.

Clean all equipment immediately after use.

APPLICATION PERFORMANCE

Even when chalking occurs, the film is not impaired in terms of protection. On freshly painted surfaces in direct contact with water during the curing process, localized staining with color change (more visible in darker colors), curing delay, and compromised product performance may occur.

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

Do not apply the product after the pot life has been exceeded.

For optimal application properties, the paint temperature must be between 69.8°F - 80.6°F before mixing and application.

Surface preparation is recommended to Sa 2½ or SSPC SP10 (ISO 8501-1 visual standard). Less stringent standards are acceptable as long as there are no contaminants, supplemented with high-pressure water cleaning.

We recommend painting only if the measured surface temperature is at least 5.4°F above the dew point.

Substrate temperature, climatic and environmental conditions during application and curing, as well as applied film thickness, may affect drying time.

Do not apply under adverse conditions, such as RH above 70% or on condensed surfaces. Small variations in color, appearance, and gloss may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

Epoxy systems may have longer curing times when exposed to low temperatures. For curing below 50°F, consult WEG Technical Department.

Information on repainting is provided as guidance and is subject to regional variations depending on local climatic conditions. For specific situations, consult WEG.

When applying by brush or roller, two or more coats may be necessary to achieve a uniform layer and recommended film thickness.

Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

On freshly painted surfaces in direct contact with water during the curing process, localized staining with color change (more visible in darker colors), curing delay, and compromised product performance may occur.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

Epoxy-based products are known for their excellent anticorrosive properties and low resistance to sun exposure. When the applied film is exposed to weathering, over time it will lose gloss, a phenomenon known as chalking, which consequently alters its color. It is important to note that, despite this chalking, the film's anticorrosive protection is not compromised.

SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: www.weg.net.

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective



gloves/protective clothing/eye protection/face protection.
Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.

Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.

The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.
