



## W-POXI HIDRO AVA 413 NOBAC

**PRODUCT DESCRIPTION:** Two-component water-soluble finish based on modified epoxy/acrylic resins. Provides an exceptional decorative look while offering high resistance to stains, dirt and chemicals. It contains fungicidal and bactericidal additives of non-toxic origin, which remain effective in the coating after drying. Its water-soluble properties allow it to be applied indoors without the need to block access to the area.

**RECOMMENDED USES:** Recommended for indoor applications on masonry, blocks, concrete or asbestos cement. Especially recommended to paint the walls of hospitals, surgical centers, laboratories, industrial and domestic kitchens and the food and pharmaceutical industries.

**CERTIFICATIONS AND APPROVAL:** This product, when supplied to comply with the RoHs Directive (Restriction of Certain Hazardous Substances) has the letter R in its description.

PACKAGING:	Component	Content	Package	Unit of measurement
	Component A	2,4	3,6	L
	Component B	1,2	1,6	L

**CHARACTERISTICS:**

**Color:** White

**Gloss:** Satin

**Volume solid:** 43 ± 2% (ISO 3233).

**Shelf-Life:** 12 months at 25°C. (77°F)

**Thickness per coat (dry):** 40 µm –50 µm

**Theoretical coverage:** 9,5 m<sup>2</sup>/l without dilution in the thickness of 45 µm dry. Without considering loss factors in application.

**Resistance to dry heat:** Maximum temperature 80 °C . The product retains its physical and chemical properties up to the temperature of 80 °C however, variations in the coating color and gloss may occur from 60 °C (140°F).

**Drying:**

	10°C (50°F)	25°C (77°F)	35°C (95°F)
--	-------------	-------------	-------------

<b>Handling:</b>	6 hours	3 hours	90 minutes
<b>Final:</b>	20 days	15 days	10 days

**Overcoating Drying:**

	10°C (50°F)	25°C (77°F)	35°C (95°F)
--	-------------	-------------	-------------

Min	24 hours	12 hours	8 hours
Max	96 hours	72 hours	48 hours

**SURFACE PREPARATION** Before starting the painting, all masonry or concrete shall be cured (28 days for cement mortar or concrete).

When the surface to be painted is very porous, it is recommended to apply previously, as sealer, a coat diluted 5% in volume with drinking water.

To obtain a totally smooth finishing, it is advisable before painting to prepare the surface with spackle or acrylic paste and afterwards sanding, following with cleaning dust and residue.

**Application over primer**

**NOTE:** Observe the product overcoating interval to apply the next coat. In case the maximum overcoating interval has been exceeded, it is necessary to manually/mechanically sand the surface to break the gloss of the previous coat and clean the sanding residues so as to provide better adhesion between the coats.

## Concrete Surface Treatment

The performance of this product is related to the degree of surface preparation. The surface must be clean, solid, free of any kind of contaminants, totally dry and rough enough to allow adhesion of the protection system.

**For further information, consult WEG Technical Department.**

### PREPARATION FOR APPLICATION

#### Mixture

Homogenize the contents of each component with mechanical or pneumatic stirring (A and B). Check there are no sediment settled at the bottom of the package. Add component B to component A, at the recommended proportion (volume), under stirring, until complete homogenization, observing the mixing ratio.

#### Mixing ratio (Volume)

2 A X 1 B.

#### Diluent Water

#### Dilution

Depending on the application method, dilute at most. 5%

Do not dilute with solvents that are not allowed by local legislation and do not exceed the recommended dilution percentage.

Only add the diluent after complete mixing of components A + B.

The quantity of diluent may vary depending on the type of equipment used and the ambient conditions during the application.

Excessive dilution of the coating may affect the formation and aspect of the film and not allow to reach the specified thickness.

Water-soluble coatings have a thixotropic characteristic by nature, and caution must be taken in the dilution process.

#### Pot life of the mixture (25°C) (77°F)

8 h

The pot life is reduced with a higher room temperature.

The pot-life test is performed according to the Brazilian standard ABNT NBR 15742; however, different volumes of coating prepared at once combined with different ambient and coating temperatures will influence the pot life, and different results than those mentioned in this data sheet may be found.

The end of the pot life does not occur by the increase in viscosity, but by loss of the system coalescence, changing its properties.

#### Induction time (25°C)

Wait 15 minutes before application.

In hot areas, we recommend consulting WEG Technical Department.

### APPLICATION FORMS

**The data below is a guide, and similar equipment may be used.**

In the spray application, make a 50% overlap in each gun pass, concluding with a cross pass. This technique is used to avoid uncovered and unprotected areas and to obtain a suitable aesthetic finish.

Recoat all sharp edges, cracks and weld beads with a brush to prevent premature failures in these areas.

Changes in nozzle sizes and pressures may be necessary to improve spraying characteristics. Before application, check if the equipment and its components are clean and in best condition. Purge the compressed air line to prevent contamination of the coating.

After mixing two-component products, if there are stops in the application, and pot life is exceeded (the coating shows variation in fluidity) it can no longer be diluted for further application.

The data below is a guide, and similar equipment may be used.

## Conventional gun:

Gun:	JGA 502/3 Devilbiss or equivalent
Fluid nozzle:	EX
Air cap:	704
Atomization pressure:	50 - 70 psi
Pressure in the tank:	10 - 20 psi
Dilution:	5%

## Airless Gun:

Use Airless:	Use at least pump 60: 1
Fluid pressure:	2000 – 3000 psi
Hose:	¼" internal diameter
Nozzle:	0,015" - 0,021"
Dilution:	Max. 5%

## Brush:

Use a brush 75 to 100 mm wide for larger surfaces and 25 to 38 mm for touch up.

## Roller:

Use a thin nap, seamless sheepskin or microfiber roller for epoxy coatings.

For application with brush and/or roller, two or more passes may be necessary to obtain a uniform layer according to the recommended film thickness per coat.

## Cleaning the equipment:

Water  
Clean all equipment immediately after use.

## NOTE:

Do not leave catalyzed product in contact with the equipment used in the application, because the coating will vary in fluidity at temperatures above specified in the pot life and will cure faster, making the cleaning difficult.

Furthermore, it is a good working practice to periodically wash the spray equipment along the day. The cleaning frequency will depend on the amount sprayed, temperature and elapsed time, including all delays.

## PERFORMANCE IN THE APPLICATION

For a good performance of the product, we recommend following the directions below:

Variations in color, aspect and gloss (more noticeable in dark colors) may occur, as well as delay in curing and low coating performance, when applied during periods of high air relative humidity, rainy days, low temperatures or drying the coating outdoor.

Epoxy-based products are known by having excellent anti-corrosion properties and low resistance to sunlight exposure. In situations of exposure of the film to the weather, over time it will present a loss of gloss known as chalking and its shade will change as a consequence. Remember that even undergoing such chalking, the film anti-corrosion protection is not impaired.

In paintings carried out in front of the sea, if exposed to sea air, we recommend to wash with fresh water between coats eliminating settled impurities.

Light colors may require more than one coat for an even coverage.

It should not be applied in adverse conditions, such as air relative humidity above 85% or on condensed surfaces. Small variations in color, appearance and gloss of the coated parts may occur in periods of high air relative humidity, rainy days, at low temperatures or in situations where the coated parts are placed to dry outdoors.

Epoxy systems may have longer curing time when exposed to low temperatures. For temperatures below 10 °C, consult WEG Technical Department.

We recommend coating only if the surface temperature is at least 3 °C (37,4°F) above the dew point temperature.

Do not apply the product after the pot life has expired.

For better application properties, the coating temperature should be between 21 - 27 °C prior to the mixing and application.

In coatings with variation in application method in the same job, the final aspect and gloss of the painted surfaces may show differences.

The temperature of the substrate, the weather and environmental conditions during the application and during the curing of the product, and the thickness of the coat may interfere in the product drying time.

For further information, consult WEG Technical Department.

## SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals.

Please read carefully all the information contained in the MSDS of this product, available at: [www.weg.net](http://www.weg.net).

Store in a covered, well-ventilated area. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists / vapors / aerosols generated during handling and / or application.

Wear protective gloves / protective clothing / eye protection / face protection.

Avoid release this product and its packaging, as well as materials used during handling and application in the environment.

---

**NOTE:**

The information contained in this technical datasheet is based upon the experience and knowledge acquired in the field by the technical team of WEG.

If using the product without previous inquiry to WEG Coating concerning its suitability for the customer's intended purpose, the customer is aware that the use shall be its exclusive responsibility, WEG not being responsible for behavior, safety, suitability or durability of the product.

Some information contained in this datasheet are estimated, and can undergo variances arising from factors outside the manufacturer's control. Thus, WEG does not guarantee and does not assume any responsibility regarding the yield, performance or any other material or personal damage resulting from the incorrect use of the products concerned or the information contained in this Technical datasheet.

The information contained in this technical datasheet is subject to periodic modification, without prior notice, due to the policy of evolution and continuous improvement of our products and services, providing solutions with quality to satisfy our customers' requirements.

---