

POLITHERM 26 R SM VARNISH VIOLET 84622 BR**Code:** 16091114**PRODUCT DESCRIPTION**

Polyester powder coating with good adhesion, flexibility, and chemical and yellowing resistance. It has high physical resistance and good weathering resistance.

RECOMMENDED USE

Coating of metal parts for industrial purposes in outdoor environments.

PROPERTIES

Due to the product's lack of hiding power, the color tone varies according to the film thickness and substrate color. Color variations between varnish batches may occur as a result of acceptable tone differences within the dye specifications.

CERTIFICATIONS AND APPROVALS

Free from heavy metals and other substances provided for in RoHS Directive 2015/863 EU of 31/03/2015.

PACKAGING

Cardboard box with 44 lb in high-density polyethylene bag.

CHARACTERISTICS OF MANUFACTURED PRODUCT

Resin	Polyester
Gloss	Bright
Finish	Smooth
Specific gravity ($\pm 0,10$)	1,22 g/cm ³
Theoretical Coverage	160.0 ft ² /lb at 1.0 mil
Mass loss during cure	Maximum 2%
Moisture content	Maximum 0.6%
Shelf life	12 months
Storage condition	It must be stored in closed containers, in cool, dry and covered places, at an ambient temperature not exceeding 86°F.

APPLICATION CHARACTERISTICS

Substrate	Ferrous metals Non-ferrous metals
Surface preparation	Ferrous : Phosphatization or nanoceramic Non-ferrous: Chromatization or nanoceramic
Surface cleaning	The performance of this product is related to the degree of surface preparation. The surface must be clean, dry and free of any contaminants. Completely remove oils, grease and fats.
Thickness	2.0 mils - 2.8 mils
Cure conditions	5 min à 392 °F (metal temperature).
Cure windows	12 min - 20 min at 356 °F 8 min - 15 min at 374 °F 5 min - 12 min at 392 °F
Application system	Electrostatic spray gun corona

NOTE:

For non-ferrous metals phosphatizing, please contact our technical service.

CHARACTERISTICS OF APPLIED PRODUCT



Test	Specification/Standard
Adhesion	5B (ASTM D 3359)
Gloss 60°	Visual standard
Impact	Minimum 43 lb.in (ASTM D2794)
Flexibility (conic mandrel)	Maximum 1/8 in (ASTM D790)

CHEMICAL RESISTANCE CHARACTERISTICS	
Test	Specification/Standard
Humidity	Minimum 1500h (ASTM D2247)
Salt spray	Minimum 700h (ASTM B117)

NOTE: In the chemical resistance tests, the substrate used was cold-rolled steel sheet with tricationic phosphate. The mechanical resistance tests were performed on degreased common steel sheet under specific curing and coating conditions for the product. The values may vary depending on the substrate used.

SAFETY PRECAUTIONS
Guidance is available in the product's Safety Data Sheet (SDS).

NOTE The information provided herein is based on our testing and experience and is intended to inform you about the product and its possible applications. The information provided in this bulletin is not intended to be complete, and the user assumes the risk of using the product for a purpose other than the specifications recommended in this bulletin without first obtaining our written confirmation of its suitability for the intended purpose. While we strive to ensure the accuracy of the information provided herein, we cannot control the quality or condition of the substrate, nor any other factors that affect the use and application of this paint. Therefore, unless we agree in writing to any condition that deviates from our recommendations, we accept no liability that may arise regarding the performance of this product. The information contained in this bulletin is subject to change without notice, based on our experience and policy of continuous development.