

# ESWF Series Combination Starters



## Economical Motor Starting Solutions

### ESWF Series Combination Starters Type E with/without CPT

High performance and optimized solutions for motor starting and control. WEG offers full voltage non-reversing combination starters, ESWF series, up to 75 HP at 460VAC (105A) with or without control power transformers for three-phase applications.



#### Standard Features

- Standard Enclosure Type: non-metallic 4X
- Control Power Transformer: with or without  
CPT primary 575V – secondary 120V  
CPT primary 480V/240V – secondary 120V
- Branch Disconnect: rotary through-the-door handle
- Short-Circuit Protection: manual motor protection
- Motor Control: magnetic IEC contactor
- Overload Protection: manual motor protection
- Standard Control Devices: HAND-OFF-AUTO switch, START and STOP pushbuttons, pilot lights
- Custom enclosure and control options available upon request


UL Combination Starter Type	Device Used for Component Function			
	Motor Disconnect	Motor Branch Circuit Protection	Motor Controller	Motor OL Relay
F	UL508 Manual Self-Protected Combination Controller		IEC Contactor	UL508 Manual Self-Protected Combination Controller




# Combination Starters – ESWF Series

## DIMENSIONS

Dimensions (inches)			
Box Size	Enclosure Size		
	H	W	D
F-1	12	12	8
F-2	16	16	8
F-3	20	20	12



### Dimensions (in) – ESWF SERIES Type 4 / 12 – Metallic Enclosure



WEG Electric Corp.  
6655 Sugarloaf Pkwy.  
Duluth, GA 30097  
Phone: 1-800-ASK-4WEG  
[www.weg.net](http://www.weg.net)

