

PRIMER EPOXI W-POXI HPP 43

PRODUCT DESCRIPTION	Fast-drying single-component epoxy primer with anticorrosive pigments.	
RECOMMENDED USE	Developed for the foundry segment.	
PACKAGING	Component A	3.6L Package containing 3.6L 20L Package containing 20L
CHARACTERISTICS	Color	Black.
	Gloss	Matte
	VOC content	530.53 g/l
	Volume Solids	44 ± 2% (ISO 3233)
	Shelf Life	12 months
	Dry Film Thickness	30 µm - 40 µm
	Dry Heat Resistance	Maximum temperature 90 °C. The product maintains its chemical properties up to a temperature of 90 °C, but from 60°C, color and gloss variations in the paint may occur.
	Theoretical Coverage	12,57 m ² /l without dilution at a dry film thickness of 35 µm. Loss factors during application are not considered.

DRYING	Drying	
		25 °C
	Manipulation	3 hours
	Final	72 hours
	Recoat Drying	
		25 °C
	Minimum	10 hours
	Maximum	72 hours

SURFACE PREPARATION	Standard Surface Preparation The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.
	Abrasive Blasting Sa 2½ blasting recommended for cast iron.

APPLICATION PREPARATION	Mixing	Homogenize the content manually, ensuring no pigment remains at the bottom of the container.
	Thinner	EPOXY DILUENT 3005
	Dilution	Depending on the application method, dilute to a maximum of 30%.
	Notes	Dilute according to recommendation. Only add the thinner after the A + B components are completely mixed.



Excessive thinning of the paint may affect film formation, appearance, and make it difficult to achieve the specified thickness.

The amount of Diluent may vary depending on the type of equipment used and environmental conditions during application. Only add Diluent after complete mixing of the other components. Do not dilute with solvents not allowed by local legislation, and do not exceed the indicated dilution percentage. Excessive dilution may affect film formation, appearance, and make it difficult to achieve the specified thickness.

Pot Life Not relevant.

APPLICATION METHODS

Conventional Spray Gun Spray gun: JGA 502 Devilbiss or equivalent
Fluid nozzle: FX
Air cap: 704.

Immersion Tanks properly prepared for paint application by immersion with continuous agitation. We recommend a tank with recirculation and cascade for homogenization and bubble removal.

Cleaning of the equipments: EPOXY DILUENT 3005

Notes Changes in pressures and nozzle sizes may be necessary to improve spraying characteristics. Purge the compressed air line to avoid paint contamination. Before application, ensure that the equipment and respective components are clean and in optimal condition. After mixing two-component products, if there are application stops and the pot life has been exceeded (paint shows variation in flow), it can no longer be re-thinned for later application. Reinforce all sharp corners, gaps, and weld beads with a brush to avoid premature failures in these areas. Clean all equipment immediately after use. Do not leave material in hoses, guns, or equipment used for spraying. Thoroughly wash all used equipment.

APPLICATION PERFORMANCE

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

Light colors may require more than one coat to achieve uniform coverage.

Painting is recommended only if surface temperature is at least 3°C above the dew point.

Substrate temperature, climatic and environmental conditions during application and curing, as well as applied film thickness, may affect drying time.

Must not be applied under adverse conditions, such as relative humidity (RH) above 85%, as color and appearance changes may occur.

Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: www.weg.net.

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.

Empty containers and materials with paint residues must be disposed of according to current



legislation. Take care of the environment.

NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.

Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.

The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.
