

Data Sheet



W-CAR POLYESTER PUTTY LIGHT

	Product Description	It is used to correct surface defects, replacing quick putty and plastic putty in a single product. It is a product with high filling power, easy application, quick drying and excellent sandability.
	Catalysis ratio	100 parts Polyester Putty. 1 to 3% by weight of hardener
	Useful life	3 at 5 minutes
	Diluent	Not apply.
	Application viscosity	Not apply.
	Application	Apply thin, successive layers with celluloid or a spatula. Application surfaces: Metal (steel, galvanized and aluminum) and fiber.
	Drying and sanding at 25°C 77°F	20 to 30 minutes for sanding. Start sanding with 80-grit sandpaper and finish with 150- and 320-grit sandpaper.
	Number of steps	The number of passes varies according to the application needs.

- Avoid excessive thicknesses;
- Use nitrile rubber gloves and safety glasses to handle the product.
- Cleaning of application equipment with acrylic/polyurethane thinner;