

## POLITHERM 30 NOBAC R TX GRAY N6.5 BR

**PRODUCT:** 12323603

**DESCRIPTION / USES:** Metallic parts coating for indoor use.

**ANTIMICROBIAL ACTION:** The NOBAC powder coatings inhibit the growth of bacteria on the painted surface with proven performance in accordance with norm JIS Z 2801: 2000. This rule evaluates the effectiveness by analyzing inhibition in 24 hours, the microbial growth of the two most common bacteria: Escherichia coli and Staphylococcus aureus. The NOBAC line was evaluated by an independent laboratory, with a microbial reduction to 99.9% according to norm JIS Z 2801: 2000.

**CHARACTERISTICS:**

<b>Resin:</b>	Epoxy / polyester
<b>Specific gravity:</b>	1,68 ± 0,10 g/cm <sup>3</sup>
<b>Stability:</b>	12 months (máx. 30°C)
<b>Observations:</b>	Free of heavy metals and other substances provided for in Directive 2015/863 EU of 03/31/2015 (RoHS).

**APPLICATION CHARACTERISTICS:**

<b>Surface:</b>	Ferrous and non-ferrous
<b>Surface preparation:</b>	Ferrous: Phosphatization Non-ferrous: Chromatization or phosphatization*
<b>Cure conditions:</b>	10 minutes at 200 °C**
<b>Thickness:</b>	70 – 90 µm
<b>Application system:</b>	Electrostatic gun

**AFTER CURE CHARACTERISTICS\*\*\*:**

TEST	METHOD	SPECIFICATION
ADHESION	WPS-3905	GR0
GLOSS	WPS-3854	Visual std.
IMPACT (REVERSE)	WPS-4130	Min. 40 kg X cm
FLEXIBILITY (CONIC MANDREL)	WPS-4856	Max. 5 mm

**CHEMICAL RESISTANCE \*\*\***

<b>Salt spray:</b>	Min. 500 h (ASTM B117 – 03)
<b>Humidity:</b>	Min. 1000 h (35°C)

\* For non-ferrous metals phosphatizing, please contact our technical service.

\*\* After stabilization on correct temperature (metal temperature).

\*\*\* The tests were conducted on degreased steel panels in accordance with the cure and thickness specifications. The figures may be change, depending on the surface characteristics. For chemical resistance tests the panels were degreased and treated with tricationic phosphat.

**IMPORTANT:** If is not possible the use of the product according to the directions given above we ask you to contact our technical service.

**STORAGE:** Fresh, dry and covered place.