

**W-POXI HIDRO AVA 41**

**PRODUCT DESCRIPTION**

Two-component waterborne finish based on modified epoxy/acrylic resins. Provides an exceptional decorative appearance while offering high resistance to stains, dirt, and chemicals. Contains non-toxic fungicidal and bactericidal additives that remain effective in the coating after drying. Its waterborne characteristic allows application in enclosed environments without the need to restrict access to the area.

Paints with antimicrobial action exclusively intended to preserve the aesthetic properties, protective performance, and durability of the applied film.

**RECOMMENDED USE**

Recommended for internal wall painting. Especially indicated for painting walls in hospitals, surgical centers, laboratories, industrial and residential kitchens, food and pharmaceutical industries.

**CERTIFICATIONS AND APPROVALS**

When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.

**PACKAGING**

**Component A** 3.6L Package containing 2.4L

**Component B** 1.5L Package containing 1.2L

**CHARACTERISTICS**

<b>Color</b>	White.
<b>Gloss</b>	Satin
<b>Volume Solids</b>	43 ± 2% (ISO 3233)
<b>Shelf Life</b>	12 months
<b>Dry Film Thickness</b>	40 µm - 50 µm
<b>Dry Heat Resistance</b>	Maximum temperature 80 °C. The product maintains its chemical properties up to a temperature of 80 °C, but from 60°C, color and gloss variations in the paint may occur.
<b>Theoretical Coverage</b>	9,56 m <sup>2</sup> /l without dilution at a dry film thickness of 45 µm. Loss factors during application are not considered.

**DRYING**

<b>Drying</b>			
	<b>10 °C</b>	<b>25 °C</b>	<b>35 °C</b>
<b>Manipulation</b>	6 hours	3 hours	90 min
<b>Final</b>	20 days	15 days	10 days
<b>Recoat Drying</b>			
	<b>10 °C</b>	<b>25 °C</b>	<b>35 °C</b>
<b>Minimum</b>	24 hours	12 hours	8 hours
<b>Maximum</b>	96 hours	72 hours	48 hours

**SURFACE PREPARATION**

**Standard Surface Preparation**

The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

**Concrete Surfaces**

Before painting, all masonry or concrete must be cured (28 days for cement mortar or concrete) and dry, without cracks, fissures, or voids, and perfectly adhered to the base or other mortar and coating layers.

For very porous surfaces, apply a 5% diluted water coat first. To achieve a completely smooth finish, prepare the surface with filler or acrylic putty, sand, and clean dust and residues before painting.



The performance of this product is associated with surface preparation. The surface must be clean, solid, free of any contaminants, fully dry, and have sufficient roughness to allow adhesion of the applied protection system.

**Over Primer**

Respect the product recoat interval. If exceeded, perform light manual/mechanical sanding to break gloss and clean dust/residues for better adhesion between coats.

**APPLICATION PREPARATION**

<b>Mixing</b>	Homogenize the content of each component using mechanical or pneumatic stirring (A and B). Ensure no sediment remains at the bottom of the container. Add component B to component A in the indicated mixing ratio under stirring until completely homogenized, respecting the mixing ratio.
<b>Mixing Ratio</b>	By volume: 2 A x 1 B.
<b>Thinner</b>	WATER
<b>Dilution</b>	Depending on the application method, dilute to a maximum of 5%.
<b>Notes</b>	Water-based paints are naturally thixotropic, requiring caution during the dilution process. The amount of Diluent may vary depending on the type of equipment used and environmental conditions during application. Only add Diluent after complete mixing of the other components. Do not dilute with solvents not allowed by local legislation, and do not exceed the indicated dilution percentage. Excessive dilution may affect film formation, appearance, and make it difficult to achieve the specified thickness.
<b>Pot Life</b>	8 h  The shelf life of the mixture is reduced as the ambient temperature increases.  The pot-life test of the mixture is carried out according to ABNT NBR 15742; however, different volumes of paint prepared at once, combined with varying ambient and paint temperatures, will affect the mixture's shelf life, potentially resulting in outcomes different from those stated in this technical bulletin.
<b>Induction Time</b>	Wait 15 minutes before application.  In very hot locations, we recommend consulting WEG's Technical Department.

**APPLICATION METHODS**

<b>Conventional Spray Gun</b>	Spray gun: JGA 502/3 Devilbiss or equivalent Fluid nozzle: EX Air cap: 704 Atomization pressure: 50 - 70 psi Tank pressure: 10 - 20 psi.
<b>Airless Spray Gun</b>	Airless: Use minimum pump 60:1 Fluid pressure: 2000 - 3000 psi Hose: 1/4" inner diameter Nozzle: 0.015" - 0.021".
<b>Roller</b>	Use a short-haired, seamless wool or synthetic roller for epoxy paints. For application with brush and/or roller, it may be necessary to apply two or more coats to achieve a uniform layer and the recommended film thickness.
<b>Brush</b>	Use a brush 75 to 100 mm wide for larger surfaces and 25 to 38 mm for touch-ups.
<b>Cleaning of the equipments:</b>	WATER



**Notes**

The data presented serves as a guide and similar equipment may be used.

Changes in pressures and nozzle sizes may be necessary to improve spraying characteristics. Purge the compressed air line to avoid paint contamination.

Do not allow catalyzed product to remain in contact with application equipment, as at temperatures above the indicated "pot life", the paint will show variation in flow and will harden, making cleaning difficult.

Before application, ensure that the equipment and respective components are clean and in optimal condition.

After mixing two-component products, if there are application stops and the pot life has been exceeded (paint shows variation in flow), it can no longer be re-thinned for later application.

In spray application, overlap each gun pass by 50%, finishing with a cross pass. This technique avoids uncovered or unprotected areas and ensures proper aesthetic finish.

Reinforce all sharp corners, gaps, and weld beads with a brush to avoid premature failures in these areas.

Clean all equipment immediately after use.

It is considered good practice to periodically wash the spraying equipment during the day. The cleaning frequency depends on the amount sprayed, temperature, and elapsed time, including all delays.

**APPLICATION PERFORMANCE**

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

Light colors may require more than one coat to achieve uniform coverage.

Do not apply the product after the pot life has been exceeded.

For optimal application properties, the paint temperature should be between 21°C and 27°C before mixing and application.

Before application, observe weather conditions: there must be no threat of rain or drizzle. Surface temperature must be at least 3°C above the dew point, and relative humidity should not exceed 85%. Adverse conditions may cause color variations and other characteristics. Consult WEG Technical Department.

Substrate temperature, climatic and environmental conditions during application and curing, as well as applied film thickness, may affect drying time.

Epoxy systems may have longer curing times when exposed to low temperatures. For curing at temperatures below 10°C, consult the WEG Technical Department.

Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

Epoxy-based products are known for their excellent anticorrosive properties and low resistance to sun exposure. When the applied film is exposed to weathering, over time it will lose gloss, a phenomenon known as chalking, which consequently alters its color. It is important to note that, despite this chalking, the film's anticorrosive protection is not compromised.

Under adverse weather conditions in indoor and/or outdoor environments with high relative humidity, rain or drizzle, low or very low temperatures, and excessively high temperatures, variations in color and other product characteristics may occur. Please consult WEG's Technical Department for more information.

**SAFETY PRECAUTIONS**

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: [www.weg.net](http://www.weg.net).

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.



Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.

Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

---

## NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.

Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.

The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.

---