


Asian Market



Electric Motors and Generators for Marine Application



The WEG Group

WEG is a globally-accepted supplier of **premium electric products for the industry**. Counting on more than **31,000 employees all over the world and a daily production of 60,000 motors**, WEG became the leading electric motor manufacturer in the Americas and one of the largest suppliers of electric and electronic products and systems in the world. With **exports to over 135 countries and revenues exceeding US\$ 3 billion**, WEG global presence is supported through its branches established in **29 countries**, manufacturing facilities and a network of distributors and representatives in the 5 continents. All WEG customers in the marine market have a long-lasting relationship with the company due to the commitment WEG has with their projects and to keep their vessels operating.



Availability = Global service network + Spare parts



Partnership = Local single contact point + Project management



Competitiveness = World class technologies + Class approvals



WEGnology = Know-how + One-stop shop

Whenever you need a reliable supplier of products for **marine applications**, count on **WEG**.





WEG Serves the Marine Industry Globally

Our global structure allows us to be closer to our customers. Over **32 subsidiaries** established in key countries are prepared to provide you with technical and commercial support. Our manufacturing plants strategically located in the main markets can serve you with short deliveries and our network of over **1,250 Authorized Service Agents** located in the five continents are fully equipped to give you prompt after sales and service support.



Global Presence

Marine Certifications



Company Overview


- Manufacturing plants in 9 countries
- Subsidiaries in 29 countries
- Over 1,250 Authorized Service Agents in the five continents

Global Product Certifications



One-stop Shop for Electric Motors and

With highly efficient and space-saving motors and generators, to fit for the toughest marine environments on earth. WEG **quality, cost-effective and environmental friendly products** are available individually and are fully customizable, making it the perfect solution for system integrators, shipyards, engineering companies, OEMs and ship owners across the globe.



Single line diagram of a typical diesel-electric propulsion system. WEG electric motors, generators, VSDs, transformers and switchboards.



WEG marine motors and generators provide maximum availability through the perfect interaction of its individual components. Our portfolio also includes special applications, for example, explosion-proof motors, break motors, motors for suction and discharge pumps on dredgers, motors for bow and azimuth thrusters, electrical motors for onboard pumps, fans, compressors as well as various winches and mooring systems.

and Generators for the Marine Industry



Motors



Efficiency and reliability on board

Reliability is what matters when electric motors are required for extreme operating conditions: humid, salt-laden and corrosive atmospheres. WEG offers a complete line of electric motors, suitably designed for several marine applications, providing **premium efficiency and high power density in a compact solution** that saves space on board.



WEG motors are fitted with special bearings, reinforced insulation windings, special marine coatings and stainless steel hardware, guaranteeing maximum performance and protection against damaging external effects, such as continuous vibration, heavy pitching and rolling motion under rough sea conditions and aggressive salt-laden ambient.

WGM Motors: Water Jacket Cooled

Designed for Tough Application Conditions


WEG Water Jacket Cooled Motors (WGM Line) can be used especially for driving machines that require constant torque even at low speeds, for long periods of operation (for instance during Dynamic Positioning). It is the right choice for demanding applications in tough Marine environments, with higher ambient temperature and limited space availability.



Advantages

- Low Noise Level
- Suitable for variable frequency drive operation
- Minimum thermal dissipation to the environment
- Compact construction
- Suitable for aggressive operating conditions

The motor cooling is guaranteed by a “water jacket” circulating system between the stator core and the outer frame, allowing a more effective heat exchange which results in a higher output power per weight ratio, therefore reducing the size of the motor. This system is ideal for variable speed applications since the thermal efficiency is optimized even on reduced speeds and where space is a concern.




Master Line

- General Purpose Motors
- Non-Sparking Motors
- Increased Safety Motors
- Pressurized Motors

The Master line (M line) motors stand out for the flexibility of their electrical and mechanical design, adapting to the strictest operating requirements in different applications. The result of this innovative development is a product with high efficiency, meeting the requirements of international standards and in line with the world market trends.

- Output: up to 50,000 kW
- Voltage: up to 14,400 V
- Cooling: open, air or water cooled

* NEMA or IEC designs



Water Cooled Motors




WEG Water Cooled motors were developed to match the increasing market demands for compact design motors with low noise level and high output power ratio per frame size. These motors meet the IE2 efficiency levels defined by IEC 60034-30:2008 Standard, thus ensuring lower energy consumption and consequently reducing their operating costs.

Standard

- Output: 18.5 to 450 kW
- Number of poles: 2 to 8 poles
- Voltage: up to 660 V
- Frequency: 50 or 60 Hz
- Service factor: 1.00 or 1.15
- Degree of protection: IP55
- Insulation class: F or H

HGF: Three Phase Induction Motor

The HGF line is differentiated by its high performance combined with low maintenance costs. This product line is ideal for operating in the toughest applications, which require increased strength and durability of motors.




Standard

- Rated output: 90 kW to 3,150 kW
- Number of poles: 2, 4, 6, 8, 10 and 12
- Frame sizes: IEC 315 to 630
- Frequency: 50 or 60 Hz
- Voltage: 380 V to 6,600 V
- Service factor: 1.00
- Insulation class: F (DT 80 K)
- Degree of protection: IP55

Electrical Motors for Special Applications

WEG develops its portfolio of products always thinking about the special features of each special application:

- Explosion-proof motors
- Brake motors
- Motors for suction and discharge pumps on dredgers
- Motors for bow and azimuth thrusters, electrical motors for onboard pumps, fans, compressors as well as various winches and mooring systems




Power Generation



Synchronous Alternators

With extensive experience in the energy sector, WEG offers a **wide range of alternators to meet the requirements of different applications** in virtually any environment. WEG alternators ensure reliable on-board power supply. In accordance with international classifications societies and in line with individual customers demands WEG delivers **fully customized solutions**, enabling our clients to stay at the forefront of their industries.

Marine Lines



AN10 Line

- Suitable for gen-sets

Technical Data

- Powers: 1,100 to 3,000 kVA
- Frames: 450 to 560 (IEC)
- Voltage: 440, 690 and 4,160 V
- Frequency: 50 to 60 Hz
- Degree of protection: IP55W
- Insulation class: 180 (H)
- Excitation: brushless
- Number of poles: 4

Features	Benefits
Special coating, components parts and windings	High resistance to corrosion, environments with oil vapor, salt, high humidity and high temperatures
Excellent performance	
Compact	Its reduced dimensions make it suitable for vessels with strict space limitations in the engine room
Flexibility	This line can be adapted to each project
Reliability	The product has special electromechanical features which ensure durability, mechanical strength and robustness



SG10 Line

- Suitable for gen-sets and main propulsion of larger vessels, drilling rigs and FPSO

Technical Data

- Powers: 3,500 to 50,000 kVA
- Voltage: 380 to 13,800 V
- Frequency: 50 to 60 Hz
- Degree of protection: IP23 or IP55
- Insulation class: 180 (H)
- Excitation: brushless
- Number of poles: 4, 6, 8, 10 and 12

Features	Benefits
Robustness	Excellent performance in severe applications
Versatility	Can be supplied with air-air and air-water cooling or open cooling
Low reactance	Meet the main load start requirements

WEG Worldwide Operations

ARGENTINA

San Francisco - Cordoba
Phone: +54 3564 421484
info-ar@weg.net

Cordoba - Cordoba
Phone: +54 351 4641366
weg-morbe@weg.com.ar

Buenos Aires
Phone: +54 11 42998000
ventas@pulverlux.com.ar

AUSTRALIA

Scoresby - Victoria
Phone: +61 3 97654600
info-au@weg.net

AUSTRIA

Markt Piesting - Wiener
Neustadt-Land
Phone: +43 2633 4040
watt@wattdrive.com

BELGIUM

Nivelles - Belgium
Phone: +32 67 888420
info-be@weg.net

BRAZIL

Jaraguá do Sul - Santa Catarina
Phone: +55 47 32764000
info-br@weg.net

CHILE

La Reina - Santiago
Phone: +56 2 27848900
info-cl@weg.net

CHINA

Nantong - Jiangsu
Phone: +86 513 85989333
info-cn@weg.net

Changzhou - Jiangsu
Phone: +86 519 88067692
info-cn@weg.net

COLOMBIA

San Cayetano - Bogota
Phone: +57 1 4160166
info-co@weg.net

ECUADOR

El Batan - Quito
Phone: +593 2 5144339
ceccato@weg.net

FRANCE

Saint-Quentin-Fallavier - Isère
Phone: +33 4 74991135
info-fr@weg.net

GERMANY

Türnich - Kerpen
Phone: +49 2237 92910
info-de@weg.net

Balingen - Baden-Württemberg
Phone: +49 7433 90410
info@weg-antriebe.de

Homburg (Efze) - Hesse
Phone: +49 5681 99520
info@akh-antriebstechnik.de

GHANA

Accra
Phone: +233 30 2766490
info@zestghana.com.gh

INDIA

Bangalore - Karnataka
Phone: +91 80 41282007
info-in@weg.net

Hosur - Tamil Nadu
Phone: +91 4344 301577
info-in@weg.net

ITALY

Cinisello Balsamo - Milano
Phone: +39 2 61293535
info-it@weg.net

JAPAN

Yokohama - Kanagawa
Phone: +81 45 5503030
info-jp@weg.net

MALAYSIA

Shah Alam - Selangor
Phone: +60 3 78591626
info@wattdrive.com.my

MEXICO

Huehuetoca - Mexico
Phone: +52 55 53214275
info-mx@weg.net

Tizayuca - Hidalgo
Phone: +52 77 97963790

NETHERLANDS

Oldenzaal - Overijssel
Phone: +31 541 571080
info-nl@weg.net

PERU

La Victoria - Lima
Phone: +51 1 2097600
info-pe@weg.net

PORTUGAL

Maia - Porto
Phone: +351 22 9477700
info-pt@weg.net

RUSSIA and CIS

Saint Petersburg
Phone: +7 812 363 2172
sales-wes@weg.net

SOUTH AFRICA

Johannesburg
Phone: +27 11 7236000
info@zest.co.za

SPAIN

Coslada - Madrid
Phone: +34 91 6553008
wegiberia@wegiberia.es

SINGAPORE

Singapore
Phone: +65 68589081
info-sg@weg.net

Singapore
Phone: +65 68622220
watteuro@watteuro.com.sg

SCANDINAVIA

Mölnlycke - Sweden
Phone: +46 31 888000
info-se@weg.net

UK

Redditch - Worcestershire
Phone: +44 1527 513800
info-uk@weg.net

UNITED ARAB EMIRATES

Jebel Ali - Dubai
Phone: +971 4 8130800
info-ae@weg.net

USA

Duluth - Georgia
Phone: +1 678 2492000
info-us@weg.net

Minneapolis - Minnesota
Phone: +1 612 3788000

VENEZUELA

Valencia - Carabobo
Phone: +58 241 8210582
info-ve@weg.net

For those countries where there is not a WEG own operation, find our local distributor at www.weg.net.



WEG Group
Jaraguá do Sul - SC - Brazil
Phone: +55 47 3276 4000
info-br@weg.net
www.weg.net

