

LACKTHERM® 1348 RED B

Code: 10001693

PRODUCT DESCRIPTION

LACKTHERM® 1348

RECOMMENDED USE

Shafts, rotors and stators.

PROPERTIES

Protection of machined metal parts.

APPLICATION SYSTEMS

Brush

Spray Gun

CERTIFICATIONS AND APPROVALS

Product in compliance with RoHS directive.

PACKAGING

Can 5 L

CHARACTERISTICS

Color	RED
Viscosity	11 - 17" CF4 (ASTM D1200/94)
Specific Gravity	0.94 +/- 0.02 g/cm³ (ASTM D1475/98)
Solids by Weight	28+/-3 % (ASTM D2697/03)
Thermal Class	155 °C (DIN 46452/77)
Dielectric Strength	60 - 90 kV/mm (IEC 60464-2)
AC/DC	AC/DC
Wire Compatibility	F-H
VOC content	678.07 g/l
Shelf Life	6 months

APPLICATION DATA

Component B	MONOCOMPONENT
Curing Time	2 h
Curing Temperature	25 °C
Film Thickness	11 µm - 17 µm
Thinner	ALKYDIC DILUENT 1021

RECOMMENDATIONS

- Keep the package closed after partial use.
- Use in a well-ventilated location.
- Keep in a cool place, away from ignition points.
- Keep the application tank closed after use.

SAFETY PRECAUTIONS

This product has been developed for industrial use and is intended to be handled by qualified professionals. Carefully read all the information contained in the Safety Data Sheet (SDS) available at: www.weg.net.

When handling this product, use the Personal Protective Equipment (PPE) as indicated in the

product's SDS.

Empty packaging and materials with product residues must be disposed of in accordance with current legislation. Preserve the environment.

NOTE

The information contained in this technical bulletin is based on the experience and field knowledge acquired by the WEG technical team. If the product is used without prior consultation with WEG regarding its suitability for the intended application, the customer acknowledges that such use is at their sole responsibility. WEG does not assume any liability for the behavior, safety, suitability, or durability of the product.

Some of the information provided in this bulletin is based on estimates and may vary due to factors beyond the manufacturer's control. Therefore, WEG makes no guarantees and assumes no responsibility for yield, performance, or for any material or personal damages resulting from the improper use of the products or the information contained in this Technical Data Sheet.

The information contained in this document is subject to periodic changes without prior notice, in line with our policy of continuous improvement and development of products and services, aiming to deliver quality solutions that meet our customers' needs.
