

Data Sheet



PRIMER HT W-30

	Product description	First medium solid 2K polyurethane. It has very fast drying and easy sanding. The product is easy to apply, has excellent filling power and excellent adhesion. Suitable for general painting, partial painting and repainting of automotive vehicles in a short time on metallic substrate .
		Shelf life 3 years
	Yield	4,5 – 5,5 m ² /L 120 - 150 μm
	Mixing Ratio	4 Parts A 1 Part B
		Pot life 20 – 30 min
	Hardener	Temperature below 15°C – Low temperatura HT 5533 hardener Ambient temperature of 25°C – Intermediate HT 5532 hardener
	Thinner	Temperature below 15°C - Thinner 5860 low temperature Ambient temperature of 25°C - Thinner intermediate 5870 Temperature above 30°C - Thinner 5880 high temperature
		Diluent 25%
	Application viscosity	18 – 22s Cup FORD 4 25°C 77°F
	Spray gun	1,7 mm a 2,0 mm 2- 3 BAR / 30 - 45 PSI
	Flash off 25°C 77°F	5 - 10 minutes
	Number of coats	2 a 3 passes 1 pass = 40 – 50 micra
	Drying 10°C 50°F Drying 25°C 77°F Drying 60°C 140°F	Touch 15 minutes handling 40 minutes Sanding 4 hours Touch 10 minutes handling 30 minutes Sanding 3 hours Sanding 20 – 30 minutes
	Infra-red Short Wave	30 minutes - 1 meter.

- Make a good degreasing before to be repainted;
- Avoid excessive weights;
- Cleaning of application materials with acrylic / polyurethane thinner;
- Paint over wash primer is recommended for better adhesion on ferrous substrates;
- Use hardener and thinner as recommended;
- Always use the set of WEG products and complements.

The technical information is the result of our experience. We guarantee the quality of the product, however, if the conditions of use are not under our control, we cannot assume any responsibility for the results obtained.