

## POLITHERM 22 SM GREEN ULB W RAL 6018 BR

**PRODUCT:** 16196542

**DESCRIPTION / USES:** Metallic parts coating for indoor use.

**CHARACTERISTICS:**

<b>Resin:</b>	Epoxy / polyester
<b>Specific gravity:</b>	1,64 ± 0,10 g/cm <sup>3</sup>
<b>Stability:</b>	06 month (máx. 30°C)

**APPLICATION CHARACTERISTICS:**

<b>Surface:</b>	Ferrous and non-ferrous
<b>Surface preparation:</b>	Ferrous: Phosphatization Non-ferrous: Chromatization or phosphatization*
<b>Cure conditions:</b>	5 minutes at 170 °C**
<b>Thickness:</b>	60 – 80 µm
<b>Application system:</b>	Electrostatic gun

**AFTER CURE CHARACTERISTICS\*\*\*:**

TEST	METHOD	SPECIFICATION
ADHESION	WPS-3905	GR0
GLOSS	WPS-3854	Min 85 UB
IMPACT (REVERSE)	WPS-4130	Min. 40 kg X cm
FLEXIBILITY (CONIC MANDREL)	WPS-4856	Max. 3 mm

**CHEMICAL RESISTANCE \*\*\***

<b>Salt spray:</b>	Min. 500 h (ASTM B117 – 73)
<b>Humidity:</b>	Min. 1000 h (35°C)

\* For non-ferrous metals phosphatizing, please contact our technical service.

\*\* After stabilization on correct temperature (metal temperature).

\*\*\* The tests were conducted on degreased steel panels in accordance with the cure and thickness specifications. The figures may be change, depending on the surface characteristics. For chemical resistance tests the panels were degreased and treated with tricationic phosphat.

**IMPORTANT:** If is not possible the use of the product according to the directions given above we ask you to contact our technical service.

**STORAGE:** Fresh, dry and covered place.