

POLITHERM 76 R SM GUM ORANGE CHEWING GUM 29902 BR

PRODUCT: 16490279

DESCRIPTION / USES: Polyester paint for application indoors, that is, without exposure to weathering. It has good resistance to yellowing, adhesion and flexibility.

ATTENTION: Due to the technical characteristics of the fluorescent pigments used, this product may contain small colored dots.

CHARACTERISTICS:

Resin:	Polyester
Specific gravity:	1,26 ± 0,10 g/cm ³
Stability:	12 month (max. 30°C)
Observations:	Free of heavy metals and other substances provided for in Directive 2015/863 EU of 03/31/2015 (RoHS).

APPLICATION CHARACTERISTICS:

Surface:	Ferrous and non-ferrous
Surface preparation:	Ferrous : Phosphatization Non-ferrous: Chromatization or phosphatization*
Cure conditions:	10 minutes at 200 °C**
Thickness:	60 – 80 µm
Application system:	Electrostatic gun

AFTER CURE CHARACTERISTICS:***

TEST	METHOD	SPECIFICATION
ADHESION	ASTM D 3359	: GR2
GLOSS @ 60°	ASTM D 523	: Min 80 UB
IMPACT (REVERSE) ADMITS FISSURES	ASTM 2794	: Min 20 kg X cm
FLEXIBILITY (CONIC MANDREL)	ASTM D 790 / ISO 178	: Max 5 mm

CHEMICAL RESISTANCE ***

Salt spray:	: Min. 500 h (ASTM B117 – 03)
Humidity:	: Min. 1000 h (35°C)

* For non-ferrous metals phosphatizing, please contact our technical service.

** After stabilization on correct temperature (metal temperature).

*** The tests were conducted on degreased steel panels in accordance with the cure and thickness specifications. The results may vary, depending on the surface characteristics. For chemical resistance testing, panels were degreased and treated with tricationic phosphat.

IMPORTANT: This coating, when properly applied and cured is suitable for the use of adhesives and sealants. However, because of the different products on the market, it requires prior testing by the user in order to select the adhesive and / or sealant appropriate.

If is not possible the use of the product according to the directions given above we ask you to contact our technical service.

STORAGE: Fresh, dry and covered place.