



W-TERM CVA 66

PRODUCT DESCRIPTION

Single-component modified silicone-based topcoat. Heat resistant up to 932°F. Can be applied directly to carbon steel.

RECOMMENDED USE

Suitable for painting chimneys, furnaces, boilers, heat exchangers, pipes, or other equipment operating at 302-932°F. 302-572°F continuous; 662-932°F up to 24 hours.

Outside the temperature and time ranges mentioned above, the product may suffer staining, film loss, or coating alterations.

CERTIFICATIONS AND APPROVALS

When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.

PACKAGING

Single Component	0.95 US gal Package containing 0.95 US gal 5.28 US gal Package containing 5.28 US gal
-------------------------	--

CHARACTERISTICS

Color	Graphite.
Gloss	Matte
VOC content	6.90 lb/gal
Volume Solids	50 ± 2% (ISO 3233)
Shelf Life	12 months
Dry Film Thickness	0.8 mils - 1.2 mils
Dry Heat Resistance	Maximum temperature 932 °F. The product maintains its chemical properties up to a temperature of 932 °F, but from 140°F, color and gloss variations in the paint may occur.
Theoretical Coverage	815.0 ft ² /gal without dilution at a dry film thickness of 1.0 mils. Loss factors during application are not considered.

DRYING

Drying	50 °F	77 °F	95 °F
	2 hours	40 min	35 min
Manipulation			

SURFACE PREPARATION

Standard Surface Preparation

The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

Remove accumulated dirt using a dry brush, clean dry cloth, compressed air blow, vacuum, or a combination of these. Remove soluble salts by washing with plenty of fresh water, preferably under low pressure (up to 5,000 psi), according to SSPC-SP12/NACE No. 5 standard.

Degreasing

Completely remove oils and greases by applying a degreasing product or according to the solvent cleaning method. Whenever cleaning surfaces with cloths, replace them to avoid saturation. Do not use cotton waste or colored cloths.

APPLICATION PREPARATION

Mixing	Homogenize the content of the container using
---------------	---



mechanical or pneumatic stirring. Ensure no sediment remains at the bottom of the container.

Thinner ALKYDIC DILUENT 1024

Dilution Depending on the application method, dilute to a maximum of 15%.

Pot Life Not relevant.

APPLICATION METHODS

Conventional Spray Gun Spray gun: JGA 502/3 Devilbiss or equivalent
 Fluid nozzle: EX
 Air cap: 704
 Atomization pressure: 60 - 65 psi
 Tank pressure: 10 - 20 psi.

Roller Not recommended.
 For application with brush and/or roller, it may be necessary to apply two or more coats to achieve a uniform layer and the recommended film thickness.

Brush Recommended only for small area touch-ups or "stripe coat" (screws, nuts, weld beads, sharp corners, and touch-ups).

Cleaning of the equipments: ALKYDIC DILUENT 1024

Notes The data presented serves as a guide and similar equipment may be used.
 Changes in pressures and nozzle sizes may be necessary to improve spraying characteristics. Purge the compressed air line to avoid paint contamination.
 Before application, ensure that the equipment and respective components are clean and in optimal condition.
 Reinforce all sharp corners, gaps, and weld beads with a brush to avoid premature failures in these areas.
 Do not leave material in hoses, guns, or equipment used for spraying. Thoroughly wash all used equipment.

APPLICATION PERFORMANCE

The adhesion test can only be carried out after full curing of the film.

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

For optimal application properties, the paint temperature must be between 69.8°F - 80.6°F before mixing and application.

We recommend painting only if the measured surface temperature is at least 5.4°F above the dew point.

Substrate temperature, climatic and environmental conditions during application and curing, as well as applied film thickness, may affect drying time.

Full cure is achieved when the equipment reaches operating temperature above 302°F.

Maximum product performance is obtained when the painted equipment enters operation at 356 to 446°F.
 It is recommended to slightly increase this temperature.

Must not be applied under adverse conditions, such as relative humidity (RH) above 85%, as color and appearance changes may occur.

For equipment operating below 302°F, a pre-cure of 30 minutes at 356°F is required.

Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.



SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: www.weg.net.

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.

Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.

Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.

The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.
