



W-THANE HIDRO HPA 50

PRODUCT DESCRIPTION

Two-component waterborne aliphatic acrylic polyurethane finish paint, glossy. Developed for anticorrosive protection and natural weathering resistance.

RECOMMENDED USE

Product that provides a high-gloss film where resistance and aesthetics are required. Combined with primer and/or epoxy intermediates, provides a highly durable system. The aliphatic acrylic polyurethane system is widely used in chemical, petrochemical, pulp and paper, sugar and alcohol, and transport industries, among others.

CERTIFICATIONS AND APPROVALS

When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.

PACKAGING

Component A	3.6L Package containing 2.88L
Component B	0.9L Package containing 0.72L

CHARACTERISTICS

Color	According to customer standard. RAL and Munsell chart.
Gloss	Gloss
VOC content	21.81 g/l
Volume Solids	46 ± 5% (ISO 3233)
Shelf Life	6 months
Dry Film Thickness	30 µm - 40 µm
Dry Heat Resistance	Maximum temperature 90 °C. The product maintains its chemical properties up to a temperature of 90 °C, but from 60°C, color and gloss variations in the paint may occur.
Theoretical Coverage	13,14 m ² /l without dilution at a dry film thickness of 35 µm. Loss factors during application are not considered.

DRYING

Drying			
	10 °C	25 °C	35 °C
Touch	4 hours	1 hour	40 min
Manipulation	12 hours	8 hours	6 hours
Final	300 hours	240 hours	168 hours
Recoat Drying			
	10 °C	25 °C	35 °C
Minimum	12 hours	8 hours	6 hours
Maximum	48 hours	48 hours	48 hours

SURFACE PREPARATION

Standard Surface Preparation

The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

Remove accumulated dirt using a dry brush, clean dry cloth, compressed air blow, vacuum, or a combination of these. Remove soluble salts by washing with plenty of fresh water, preferably under low pressure (up to 5,000 psi), according to SSPC-SP12/NACE No. 5 standard.

Over Primer

The product can be applied over a specific primer in order to form an appropriate coating system.



Respect the primer recoat interval before applying the product. If exceeded, perform sanding according to the technical bulletin. Painting over primer with exceeded interval may have adhesion lower than specified by Petrobras N2913 and ASTM D4541.

APPLICATION PREPARATION

Mixing	Homogenize the content of component A using mechanical stirring. Ensure no sediment remains at the bottom of the container. Add component B to component A in the indicated (volume) proportions under stirring until completely homogenized, respecting the mixing ratio.
Mixing Ratio	By volume: 2 A x 1 B.
Thinner	WATER
Dilution	Depending on the application method, dilute to a maximum of 10%.
Notes	Water-based paints are naturally thixotropic, requiring caution during the dilution process. The amount of Diluent may vary depending on the type of equipment used and environmental conditions during application. Only add Diluent after complete mixing of the other components. Do not dilute with solvents not allowed by local legislation, and do not exceed the indicated dilution percentage. Excessive dilution may affect film formation, appearance, and make it difficult to achieve the specified thickness.
Pot Life	2 h The shelf life of the mixture is reduced as the ambient temperature increases. The pot-life test of the mixture is carried out according to ABNT NBR 15742; however, different volumes of paint prepared at once, combined with varying ambient and paint temperatures, will affect the mixture's shelf life, potentially resulting in outcomes different from those stated in this technical bulletin.
Induction Time	Wait 7 to 10 minutes before application. In very hot locations, we recommend consulting WEG's Technical Department.

APPLICATION METHODS

Conventional Spray Gun	Spray gun: JGA 502/3 Devilbiss or equivalent Fluid nozzle: EX Air cap: 704 Atomization pressure: 60 - 65 psi Tank pressure: 10 - 20 psi.
Airless Spray Gun	Airless: Use minimum pump 60:1 Fluid pressure: 1200 - 2200 psi Hose: 3/8" inner diameter Nozzle: 0.015" - 0.021".
Roller	Use a short-haired, seamless wool or synthetic roller for epoxy paints. For application with brush and/or roller, it may be necessary to apply two or more coats to achieve a uniform layer and the recommended film thickness.
Brush	Recommended only for small area touch-ups or "stripe coat" (screws, nuts, weld beads, sharp corners, and touch-ups).
Cleaning of the equipments:	WATER
Notes	The data presented serves as a guide and similar equipment may be used. Changes in pressures and nozzle sizes may be



necessary to improve spraying characteristics. Purge the compressed air line to avoid paint contamination.

Do not allow catalyzed product to remain in contact with application equipment, as at temperatures above the indicated "pot life", the paint will show variation in flow and will harden, making cleaning difficult.

Before application, ensure that the equipment and respective components are clean and in optimal condition.

After mixing two-component products, if there are application stops and the pot life has been exceeded (paint shows variation in flow), it can no longer be re-thinned for later application.

Reinforce all sharp corners, gaps, and weld beads with a brush to avoid premature failures in these areas.

Clean all equipment immediately after use.

APPLICATION PERFORMANCE

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

Light colors may require more than one coat to achieve uniform coverage.

Do not apply the product after the pot life has been exceeded.

For optimal application properties, the paint temperature should be between 21°C and 27°C before mixing and application.

Substrate temperature, climatic and environmental conditions during application and curing, as well as applied film thickness, may affect drying time.

Must not be applied under adverse conditions, such as relative humidity (RH) above 85%, as color and appearance changes may occur.

Polyurethane systems (components A and B) are sensitive to relative humidity, which may cause defects in the dry film and reduction in pot life. After use, keep containers closed and protected.

A sudden reduction in gloss may occur if components A and B are not well homogenized.

Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

On freshly painted surfaces in direct contact with water during the curing process, localized staining with color change (more visible in darker colors), curing delay, and compromised product performance may occur.

Product not recommended for internal tank painting.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: www.weg.net.

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.

Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.

Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the



products in question or from the information contained in this Technical Bulletin.
The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.
