

POLITHERM 27 SM RED W RAL 3020 SM

PRODUCT: 16115842

DESCRIPTION / USES: Metallic parts coating for outdoor use.

CHARACTERISTICS:

Resin:	Polyester
Specific gravity:	1,66 ± 0,10 g/cm ³
Stability:	12 month (max. 30°C)

APPLICATION CHARACTERISTICS:

Surface:	Ferrous and non-ferrous
Surface preparation:	Ferrous : Phosphatization Non-ferrous: Chromatization or phosphatization*
Cure conditions:	5 minutes at 200 °C**
Thickness:	60 – 80 µm
Application system:	Electrostatic gun

AFTER CURE CHARACTERISTICS:***

TEST	METHOD	SPECIFICATION
ADHESION	ASTM D 3359	: GR0
GLOSS @ 60°	ASTM D 523	: 50 ± 5 UB
IMPACT (REVERSE)	ASTM 2794	: Min 50 kg X cm
FLEXIBILITY (CONIC MANDREL)	ASTM D 790 / ISO 178	: Max 3 mm

CHEMICAL RESISTANCE ***

Salt spray:	: Min. 500 h (ASTM B117 – 03)
Humidity:	: Min. 1000 h (35°C)

* For non-ferrous metals phosphatizing, please contact our technical service.

** After stabilization on correct temperature (metal temperature).

*** The tests were conducted on degreased steel panels in accordance with the cure and thickness specifications. The results may vary, depending on the surface characteristics. For chemical resistance testing, panels were degreased and treated with tricationic phosphat.

IMPORTANT: This coating, when properly applied and cured is suitable for the use of adhesives and sealants. However, because of the different products on the market, it requires prior testing by the user in order to select the adhesive and / or sealant appropriate.

If is not possible the use of the product according to the directions given above we ask you to contact our technical service.

STORAGE: Fresh, dry and covered place.