



POLITHERM 96 WFQ R MT MIXER BROWN 75212 MA

Code: 18027104

PRODUCT DESCRIPTION

QUALICOAT-approved polyester powder coating, offering excellent adhesion and flexibility, as well as good chemical and yellowing resistance. It has high physical resistance and excellent weathering resistance.

RECOMMENDED USE

QUALICOAT-approved coating for metal parts intended for industrial and architectural applications in outdoor environments.

PROPERTIES

Due to the technical characteristics of this product, properties such as gloss, roughness and texture may vary depending on the applied film thickness and application conditions, such as voltage, flow rate, spray gun distance and grounding.

This coating, when properly applied and cured is suitable for the use of adhesives and sealants. However, because of the different products on the market, it requires prior testing by the user in order to select the adhesive and / or sealant appropriate.

CERTIFICATIONS AND APPROVALS

Free from heavy metals and other substances provided for in RoHs Directive 2015/863 EU of 31/03/2015.

The Politherm 96 WFQ line is QUALICOAT APPROVAL N° P-1717 Class 1, Category 1 certified and complies with AAMA 2603 standard.

PACKAGING

Cardboard box with 55 lb in high-density polyethylene bag.

CHARACTERISTICS OF MANUFACTURED PRODUCT

Resin	Polyester
Gloss	Matte
Finish	Microtexture
Specific gravity (± 0,10)	1,48 g/cm³
Theoretical Coverage	131.9 ft²/lb at 1.0 mil
Mass loss during cure	Maximum 2%
Moisture content	Maximum 0.6%
Shelf life	12 months
Storage condition	It must be stored in closed containers, in cool, dry and covered places, at an ambient temperature not exceeding 86°F.

APPLICATION CHARACTERISTICS

Substrate	Ferrous metals Non-ferrous metals
Surface preparation	Aluminum: Chromatization. Aluminum: Nanoceramic Galvanized steel: Phosphatization.
Surface cleaning	The performance of this product is related to the degree of surface preparation. The surface must be clean, dry and free of any contaminants. Completely remove oils, grease and fats.
Thickness	2.8 mils - 3.5 mils
Cure conditions	10 min à 392 °F (metal temperature).



Cure windows 12 min - 20 min at 374 °F
10 min - 15 min at 392 °F

Application system Electrostatic spray gun corona

CHARACTERISTICS OF APPLIED PRODUCT

Test	Specification/Standard
Adhesion	5B (ASTM D 3359)
Gloss 60°	Visual standard
Impact	Minimum 43 lb.in (ASTM D2794)
Flexibility (conic mandrel)	Maximum 1/8 in (ASTM D790)
Cupping test	Minimum 1/5 in (EN ISO 1520)
Indentation	Minimum 80 (EN ISO 2815)
Bend test (5mm diameter cilinder)	No cracking or detachment (EN ISO 1519)

CHEMICAL RESISTANCE CHARACTERISTICS

Test	Specification/Standard
Humidity	Minimum 2000h (ASTM D2247)
Acetic salt spray	Minimum 1000h (ISO 9227)
Salt spray	Minimum 1000h (ASTM B117)

NOTE:

Chemical resistance and mechanical strength tests were performed on aluminum sheets pretreated with zirconium nanoceramic under curing conditions and coatings specific to the product. Values may vary depending on the substrate and pretreatment used.

SAFETY PRECAUTIONS

Guidance is available in the product's Safety Data Sheet (SDS).

NOTE

The information provided herein is based on our testing and experience and is intended to inform you about the product and its possible applications. The information provided in this bulletin is not intended to be complete, and the user assumes the risk of using the product for a purpose other than the specifications recommended in this bulletin without first obtaining our written confirmation of its suitability for the intended purpose. While we strive to ensure the accuracy of the information provided herein, we cannot control the quality or condition of the substrate, nor any other factors that affect the use and application of this paint. Therefore, unless we agree in writing to any condition that deviates from our recommendations, we accept no liability that may arise regarding the performance of this product. The information contained in this bulletin is subject to change without notice, based on our experience and policy of continuous development.