



## W-THANE HBA 50

### PRODUCT DESCRIPTION

High-build, high-solids aliphatic acrylic polyurethane finish paint. Low VOC. Provides barrier-type anticorrosive protection, high concrete waterproofing, chemical resistance, and continuous weathering resistance.

### RECOMMENDED USE

The product can be used in aggressive industrial environments, chemical, pulp and paper, petrochemical industries, metal structures, and external painting of tanks, equipment, and light to moderate traffic floors.

### CERTIFICATIONS AND APPROVALS

This product complies with Mexican Official Standard NOM-050-SCFI-2004 and NOM-003-SSA1-2018.

When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.

### PACKAGING

|                    |                                                                                          |
|--------------------|------------------------------------------------------------------------------------------|
| <b>Component A</b> | 0.95 US gal Package containing 0.82 US gal<br>5.28 US gal Package containing 4.60 US gal |
| <b>Component B</b> | 0.24 US gal Package containing 0.12 US gal<br>1.06 US gal Package containing 0.69 US gal |

### CHARACTERISTICS

|                             |                                                                                                                                                                                                       |
|-----------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Color</b>                | According to customer standard.<br>RAL and Munsell chart.<br>RAL, Munsell, or according to the customer's standard.                                                                                   |
| <b>Gloss</b>                | Gloss (>80 UB) W-THANE HBA 501<br>Semi-gloss (60 - 80 UB) W-THANE HBA 502<br>Semi-matte (30 - 60 UB) W-THANE HBA 503<br>Matte (15 - 30 UB) W-THANE HBA 504<br>Ultra-matte (0 - 15 UB) W-THANE HBA 505 |
| <b>VOC content</b>          | 4.5 (lb/gal).<br>Note: The average of VOC on the line can vary depending on the color.                                                                                                                |
| <b>Volume Solids</b>        | 68 ± 2% (ISO 3233)                                                                                                                                                                                    |
| <b>Shelf Life</b>           | 24 months                                                                                                                                                                                             |
| <b>Dry Film Thickness</b>   | 3.0 mils - 4.9 mils                                                                                                                                                                                   |
| <b>Dry Heat Resistance</b>  | Maximum temperature 194 °F.<br>The product maintains its chemical properties up to a temperature of 194 °F, but from 140°F, color and gloss variations in the paint may occur.                        |
| <b>Theoretical Coverage</b> | 277.1 ft <sup>2</sup> /gal without dilution at a dry film thickness of 3.9 mils. Loss factors during application are not considered.                                                                  |

### DRYING

|                      |              |              |              |
|----------------------|--------------|--------------|--------------|
| <b>Drying</b>        |              |              |              |
|                      | <b>50 °F</b> | <b>77 °F</b> | <b>95 °F</b> |
| <b>Touch</b>         | 8 hours      | 6 hours      | 4 hours      |
| <b>Manipulation</b>  | 12 hours     | 10 hours     | 8 hours      |
| <b>Final</b>         | 180 hours    | 168 hours    | 150 hours    |
| <b>Recoat Drying</b> |              |              |              |
|                      | <b>50 °F</b> | <b>77 °F</b> | <b>95 °F</b> |
| <b>Minimum</b>       | 24 hours     | 8 hours      | 5 hours      |
| <b>Maximum</b>       | 21 days      | 20 days      | 15 days      |

### SURFACE PREPARATION

#### Standard Surface Preparation

The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

The surface must be clean, dry, and free of contaminants. Completely remove oils, greases, and fats according to SSPC-SP1.

## Over Primer

The product must be applied over a specific primer. The primer must be clean, dry, and free of contaminants. The topcoat must be applied within the primer recoat interval. Consult the primer technical bulletin for correct application.

Respect the product recoat interval. If exceeded, perform light manual/mechanical sanding to break gloss and clean dust/residues for better adhesion between coats.

## APPLICATION PREPARATION

|                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
|-----------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Mixing</b>               | Homogenize the content of each component using mechanical or pneumatic stirring (A and B). Ensure no sediment remains at the bottom of the container. Add component B to component A in the indicated mixing ratio under stirring until completely homogenized, respecting the mixing ratio.                                                                                                                                                                                                                                                                                                                                                                                                          |
| <b>Mixing Ratio</b>         | By weight: 100 A x 12 B.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| <b>Thinner</b>              | PU DILUENT 5003                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| <b>Alternative Thinners</b> | <p>PU Thinner 5003 - Recommended for temperatures below 77°F.</p> <p>PU Thinner 5007 - Recommended for temperatures above 95°F and oven drying.</p> <p>PU Thinner 5007 - Recommended for temperatures above 68°F.</p> <p>PU Thinner 5004 - Recommended for temperatures between 77-95°F.</p>                                                                                                                                                                                                                                                                                                                                                                                                          |
| <b>Dilution</b>             | Depending on the application method, dilute to a maximum of 10%.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| <b>Notes</b>                | <p>Dilute according to recommendation.</p> <p>Only add the thinner after the A + B components are completely mixed.</p> <p>Excessive thinning of the paint may affect film formation, appearance, and make it difficult to achieve the specified thickness.</p> <p>The amount of Diluent may vary depending on the type of equipment used and environmental conditions during application. Only add Diluent after complete mixing of the other components. Do not dilute with solvents not allowed by local legislation, and do not exceed the indicated dilution percentage. Excessive dilution may affect film formation, appearance, and make it difficult to achieve the specified thickness.</p> |
| <b>Pot Life</b>             | <p>4 h</p> <p>The shelf life of the mixture is reduced as the ambient temperature increases.</p> <p>The pot-life test of the mixture is carried out according to ABNT NBR 15742; however, different volumes of paint prepared at once, combined with varying ambient and paint temperatures, will affect the mixture's shelf life, potentially resulting in outcomes different from those stated in this technical bulletin.</p>                                                                                                                                                                                                                                                                      |
| <b>Induction Time</b>       | Wait 15 to 20 minutes before application.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |



In very hot locations, we recommend consulting WEG's Technical Department.

## APPLICATION METHODS

### Conventional Spray Gun

Spray gun: JGA 502/3 Devilbiss or equivalent  
Fluid nozzle: EX  
Air cap: 704  
Atomization pressure: 50 - 70 psi  
Tank pressure: 10 - 20 psi.

### Airless Spray Gun

Airless: Use minimum pump 60:1  
Fluid pressure: 1500 - 2500 psi  
Hose: 1/4" inner diameter  
Nozzle: 0.015" - 0.021".

### Roller

Use a short-haired, seamless wool or synthetic roller for epoxy paints.  
For application with brush and/or roller, it may be necessary to apply two or more coats to achieve a uniform layer and the recommended film thickness.

### Brush

Recommended only for small area touch-ups or "stripe coat" (screws, nuts, weld beads, sharp corners, and touch-ups).

### Cleaning of the equipments:

PU DILUENT 5003

### Notes

Do not allow catalyzed product to remain in contact with application equipment, as at temperatures above the indicated "pot life", the paint will show variation in flow and will harden, making cleaning difficult.

## APPLICATION PERFORMANCE

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

Light colors may require more than one coat to achieve uniform coverage.

Do not apply the product after the pot life has been exceeded.

For optimal application properties, the paint temperature must be between 69.8°F - 80.6°F before mixing and application.

Before application, observe weather conditions: there must be no threat of rain or drizzle. Surface temperature must be at least 37.4°F above the dew point, and relative humidity should not exceed 85%. Adverse conditions may cause color variations and other characteristics. Consult WEG Technical Department.

We recommend painting only if the measured surface temperature is at least 5.4°F above the dew point.

Substrate temperature, climatic and environmental conditions during application and curing, as well as applied film thickness, may affect drying time.

Polyurethane systems (components A and B) are sensitive to relative humidity, which may cause defects in the dry film and reduction in pot life. After use, keep containers closed and protected.

Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

Under adverse weather conditions in indoor and/or outdoor environments with high relative humidity, rain or drizzle, low or very low temperatures, and excessively high temperatures, variations in color and other product characteristics may occur. Please consult WEG's Technical Department for more information.

## SYSTEM COMPATIBILITY AND MAINTENANCE REPAINTING

The primer repainting interval must be respected for the application of the topcoat. If the maximum interval indicated is exceeded, manual/mechanical sanding with sandpaper to remove gloss is necessary. The primer surface must be dry and free of contaminants.



In situations where the nature of the primer is unknown, it is recommended to test the product's compatibility on a small area; it must be ensured that the original material is well adhered. All non-adhered paint must be removed; areas with corrosion or applications over aged paints must be treated according to technical guidance.

Direct application of the product over zinc-rich primers based on ethyl silicate, alkyd primers, coal tar-based paints, and other single-component primers is not recommended. When topcoat application over any of the above primers is required, we recommend applying a suitable intermediate product.

## SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: [www.weg.net](http://www.weg.net).

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.

Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

## NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.

Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.

The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.