

## W-ESTER CVP 96

### PRODUCT DESCRIPTION

Single-component epoxy ester primer, air-drying. Offers good adhesion and flexibility.

### RECOMMENDED USE

Primer widely used for painting machinery and equipment. Used for painting electric motor shafts over impregnated windings.

### CERTIFICATIONS AND APPROVALS

When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.

### PACKAGING

#### Single Component

0.9L Package containing 0.9L  
3.6L Package containing 3.6L  
20L Package containing 20L

### CHARACTERISTICS

|                             |                                                                                                                                              |
|-----------------------------|----------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Color</b>                | Red Oxide.                                                                                                                                   |
| <b>Gloss</b>                | Matte (15 - 30 UB) W-ESTER CVP 964<br>Ultra-matte (0 - 15 UB) W-ESTER CVP 965                                                                |
| <b>VOC content</b>          | 634.32 g/l<br>674.13 g/l                                                                                                                     |
| <b>Volume Solids</b>        | 40 ± 5% (ISO 3233)                                                                                                                           |
| <b>Shelf Life</b>           | 12 months                                                                                                                                    |
| <b>Dry Film Thickness</b>   | 20 µm - 30 µm                                                                                                                                |
| <b>Dielectric Strength</b>  | 20-30 kV/mm                                                                                                                                  |
| <b>Dry Heat Resistance</b>  | Maximum temperature 200 °C.<br>Organic coatings can undergo changes in color, gloss, and adhesion when exposed to temperatures above 200 °C. |
| <b>Theoretical Coverage</b> | 16,00 m <sup>2</sup> /l without dilution at a dry film thickness of 25 µm. Loss factors during application are not considered.               |

### DRYING

#### Drying

**25 °C**

|                     |           |
|---------------------|-----------|
| <b>Touch</b>        | 25 min    |
| <b>Manipulation</b> | 24 hours  |
| <b>Final</b>        | 168 hours |

#### Recoat Drying

**25 °C**

|                |          |
|----------------|----------|
| <b>Minimum</b> | 10 hours |
| <b>Maximum</b> | 30 days  |

### SURFACE PREPARATION

#### Standard Surface Preparation

The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

The surface must be clean, dry, and free of contaminants. Completely remove oils, greases, and fats according to SSPC-SP1.

Remove accumulated dirt using a dry brush, clean dry cloth, compressed air blow, vacuum, or a combination of these. Remove soluble salts by washing with plenty of fresh water, preferably under low pressure (up to 5,000 psi), according to SSPC-SP12/NACE No. 5 standard.



#### Degreasing

Completely remove oils and greases by applying a degreasing product or according to the solvent cleaning method. Whenever cleaning surfaces with cloths, replace them to avoid saturation. Do not use cotton waste or colored cloths.

#### Abrasive Blasting

Perform abrasive blasting to near-white metal, Sa 2½ grade, according to ISO 8501-1 visual standard (A Sa 2½, B Sa 2½, C Sa 2½, D Sa 2½), or according to SSPC-SP10/NACE No. 2, visual standard SSPC-VIS 1 (A SP10, B SP10, C SP10, D SP10, G1 SP10, G2 SP10, G3 SP10).

Inspect the freshly blasted surface, observing defects that may appear after treatment. Correct them by grinding, filling with welds and/or epoxy putty.

For areas near marine environments, wash with fresh water at low pressure (minimum 3,000 psi) before abrasive blasting. In some cases, repeat washing after blasting to remove soluble contaminants and perform a new abrasive blasting.

If oxidation occurs between the end of abrasive blasting and coating application, the surface must be blasted again until the specified visual standard is achieved.

#### Carbon Steel Surfaces

Hard surface layers (e.g., layers resulting from flame cutting) must be removed by grinding before starting abrasive blasting.

All welds must be inspected and, if necessary, repaired before completing abrasive blasting. Porosities, cavities, weld splatter, etc., must be repaired with proper mechanical treatment or welding repair. In other areas, round edges and sharp corners (r # 2 mm, ISO 8501-3).

#### Phosphated Surfaces

Carry out the coating conversion process by phosphating, using either zinc or tricationic phosphate, with a mass between 2.0 g/m² and 4.0 g/m². Follow the sequential steps: degreasing; washing; pickling; washing; conditioner; phosphating; washing; passivation; deionized water rinse; drying.

NOTE: Surface preparation must be performed according to all sequential steps relevant to the phosphating process, following the recommendations of the pretreatment manufacturer.

#### Over Primer

Respect the product recoat interval. If exceeded, perform light manual/mechanical sanding to break gloss and clean dust/residues for better adhesion between coats.

### APPLICATION PREPARATION

|                 |                                                                                                                                                                                                                                                                                                                                                                                                                                |
|-----------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Mixing</b>   | Homogenize the content of the container using mechanical or pneumatic stirring. Ensure no sediment remains at the bottom of the container.                                                                                                                                                                                                                                                                                     |
| <b>Thinner</b>  | ALKYDIC DILUENT 1024                                                                                                                                                                                                                                                                                                                                                                                                           |
| <b>Dilution</b> | Depending on the application method, dilute to a maximum of 25%.                                                                                                                                                                                                                                                                                                                                                               |
| <b>Notes</b>    | The amount of Diluent may vary depending on the type of equipment used and environmental conditions during application. Only add Diluent after complete mixing of the other components. Do not dilute with solvents not allowed by local legislation, and do not exceed the indicated dilution percentage. Excessive dilution may affect film formation, appearance, and make it difficult to achieve the specified thickness. |
| <b>Pot Life</b> | Not relevant.                                                                                                                                                                                                                                                                                                                                                                                                                  |

### APPLICATION METHODS

|                               |                                                                                                                                                      |
|-------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Conventional Spray Gun</b> | Spray gun: JGA 502/3 Devilbiss or equivalent<br>Fluid nozzle: EX<br>Air cap: 704<br>Atomization pressure: 50 - 70 psi<br>Tank pressure: 10 - 20 psi. |
| <b>Airless Spray Gun</b>      | Airless: Use minimum pump 60:1<br>Fluid pressure: 1500 - 2500 psi<br>Hose: 1/4" inner diameter<br>Nozzle: 0.013" - 0.017".                           |



|                                    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
|------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Roller</b>                      | For application with brush and/or roller, it may be necessary to apply two or more coats to achieve a uniform layer and the recommended film thickness.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| <b>Brush</b>                       | Not recommended.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| <b>Immersion</b>                   | Consult technical assistance for immersion.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| <b>Cleaning of the equipments:</b> | ALKYDIC DILUENT 1024                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| <b>Notes</b>                       | <p>The data presented serves as a guide and similar equipment may be used.</p> <p>Changes in pressures and nozzle sizes may be necessary to improve spraying characteristics. Purge the compressed air line to avoid paint contamination.</p> <p>Before application, ensure that the equipment and respective components are clean and in optimal condition.</p> <p>After mixing two-component products, if there are application stops and the pot life has been exceeded (paint shows variation in flow), it can no longer be re-thinned for later application.</p> <p>Reinforce all sharp corners, gaps, and weld beads with a brush to avoid premature failures in these areas.</p> |

## APPLICATION PERFORMANCE

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

For optimal application properties, the paint temperature should be between 21°C and 27°C before mixing and application.

Painting is recommended only if surface temperature is at least 3°C above the dew point.

Substrate temperature, climatic and environmental conditions during application and curing, as well as applied film thickness, may affect drying time.

Must not be applied under adverse conditions, such as relative humidity (RH) above 85%, as color and appearance changes may occur.

The theoretical yield is calculated based on the volume solids without thinning and does not include losses due to roughness, part geometry, application methods, application conditions, inadequate thickness, or applicator techniques.

Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

## SYSTEM COMPATIBILITY AND MAINTENANCE REPAINTING

The primer repainting interval must be respected for the application of the topcoat. If the maximum interval indicated is exceeded, manual/mechanical sanding with sandpaper to remove gloss is necessary. The primer surface must be dry and free of contaminants.

## SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: [www.weg.net](http://www.weg.net).

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.

Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

## NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or



durability of the product.

Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.

The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.

---