


W21 MEPS Korea

South Korea IE3

Reliability &
Efficiency



W21 Premium Efficiency three phase induction motor

Minimum Energy Performance Standards (MEPS)


As a consequence of need to reduce energy consumption and carbon dioxide emissions, the Ministry of Knowledge Economy (MKE) of South Korea and Korea Energy Management Corporation (KEMCO) have drafted and implemented the regulation on Energy Efficiency Labeling and Standards (MKE-2015-28, KS C IEC60034) for electric motors. Mandatory MEPS for electric motors is:

Applicable to :	Not applicable to :
Ratings from 0.75 to 200 kW (2, 4, 6 and 8 poles)	TEAO and TENV designs
Ratings from 225 to 375 kW (4 and 6 poles)	Duty type different from S1
Frequency: 60 Hz	Motors wholly immersed in a liquid
Voltage up to 600 V	Design C and D
Closed and open enclosures	Multi-speed motors
Inverter-driven motor with continuous operating (fan, blower and pump)	Thrust or sleeve bearings

The measurement method follows the determination of loss and efficiency of the three phase electric motors in accordance with KS C IEC 60034-2-1. The motors with efficiency lower than defined in MEPS (tables below) are subject to restrictions on production and sales in South Korean market. WEG MEPS SK IE3 motors have output range 0.75kW to 200kW, 2, 4 and 6 poles.

Output (kW)	IE3			
	2 Poles	4 Poles	6 Poles	8 Poles
0.75	77.0	83.5	82.5	75.5
1.5	85.5	86.5	88.5	84.0
2.2	86.5	89.5	89.5	85.5
3.7	88.5	89.5	89.5	86.5
5.5	89.5	91.7	91.0	86.5
7.5	90.2	91.7	91.0	89.5
11	91.0	92.4	91.7	89.5
15	91.0	93.0	91.7	90.2
18.5	91.7	93.6	93.0	90.2
22	91.7	93.6	93.0	91.7
30	92.4	94.1	94.1	91.7

Output (kW)	IE3			
	2 Poles	4 Poles	6 Poles	8 Poles
37	93.0	94.5	94.1	92.4
45	93.6	95.0	94.5	92.4
55	93.6	95.4	94.5	93.6
75	94.1	95.4	95.0	93.6
90	95.0	95.4	95.0	94.1
110	95.0	95.8	95.8	94.1
132	95.4	95.8	95.8	94.5
160	95.4	96.2	95.8	94.5
200	95.8	96.2	95.8	94.5
225	-	96.2	95.8	-
260	-	96.2	95.8	-
300	-	96.2	95.8	-
335	-	96.2	95.8	-
375	-	96.2	95.8	-



Attention:


Motors without this label will not be allowed through Korean customs.

Name Plates


Main and additional nameplates are made of AISI 304 stainless steel and all information is laser engraved on them. Important and useful information is included in such nameplates like serial number, output power, voltage, frequency, rated current, degree of protection, power factor, thermal class, bearing type, type of grease and lubrication intervals. Nameplate model 1 is for motor with frame up to 200 and nameplate model 2 is for motor with frame above 200.



Model 2



Model 1



Specifications

Frame			80	90S	90L	100L*	112M*	132S	132M	160M	160L
Mechanical Features											
Name Plate Marks:			KS C 4202; CE; IEC 60034;								
Mounting			B3R(E)								
Frame Material			Cast Iron FC-200								
Protection Degree			IP55								
Grounding			Single Grounding (Grounding Internal in the Terminal Box)								
Cooling System			TEFC								
Fan Material	2-4P		Plastic								
	6-8P		Plastic								
Fan Cover Material			Steel Plate								
End Shields Material			Cast Iron FC-200								
Drain			Automatic rubber drain plug								
Bearings	Closed/Front Clearance		ZZ							C3	
	Closed/Rear Clearance		ZZ							Z-C3	
	Clamping		WITHOUT							DE bearing locked with inner bearing cap and fitted with wave washer in the NDE bearing	
	Front side	2P	6204	6205	6205	6206	6207	6308	6308	6309	6309
		4 - 8P									
	Rear side	2P	6203	6204	6204	6205	6206	6207	6207	6209	6209
4 - 8P											
Bearing Sealing			V'ring								
Joint Sealing			Without								
Regreasing	Grease 2P		Polirex EM								
	Grease 4P and above		Polirex EM								
	Grease Nipple		Without								
Terminal Block			BMC 6 Terminals								
Terminal Box Material			Cast Iron FC-200								
Additional Terminal Box			Without								
Cable Entrance	Main Size		2xM20x1.5	2xM25x1.5			2xM32x1.5			2xM40x1.5	
	Plug		Plastic and Threaded Plug								
Shaft	Material		SAE 1040/45								
	Threaded Hole	2P	M6	M8	M8	M10	M10	M12	M12	M16	M16
		4 - 8P									
Key			Type A								
Vibration			Level A								
Balancing			Standard Balance with 1/2 Key								
Name Plate Material			Stainless Steel AISI 304								
Painting	Plan		207A							203A	
	Color		RAL 5009								
Electrical Features											
Design			N								
Voltage			380V with 6 Terminals								
Winding	Material		Copper								
	Impregnation		Dip and Bake								
	Insulation Class		F								
Service Factor			1.25								
Rotor			Squirrel Cage Aluminum								
Thermal Protection			None							Thermistor 155°C Shutdown	

Frame			180M*	180L	200M	200L	225S/M*	250S/M*	280S/M	315S/M	355M/L
Mechanical Features											
Name Plate Marks:			KS C 4202; CE; IEC 60034;								
Mounting			B3R(E)								
Frame Material			Cast Iron FC-200								
Protection Degree			IP55								
Grounding			Single Grounding (Grounding Internal in the Terminal Box)				Double Grounding (Internal in the Terminal Box and on the Frame)				
Cooling System			TEFC								
Fan Material		2-4P	Plastic								Aluminum
		6P	Plastic								
Fan Cover Material			Steel Plate								
End Shields Material			Cast Iron FC-200								
Drain			Automatic rubber drain plug								
Bearing	Closed/Front Clearance		C3								
	Closed/Rear Clearance		Z-C3				C3				
	Clamping		DE bearing locked with inner bearing cap and fitted with wave washer in the NDE bearing				DE bearing locked with inner and outer bearing caps and fitted with pre-load springs in the NDE bearing				
	Front side	2P	6311	6311	6312	6312	6314	6314	6314	6314	6316
		4 - 6P							6316	6319	6322
	Rear side	2P	6211	6211	6212	6212	6314	6314	6314	6314	6314
		4 - 6P							6316	6316	6319
Bearing Sealing			V'ring								
Joint Sealing			Without								
Greasing	Grease 2P		Polyrex EM								
	Grease 4P and above										
	Grease Nipple		Without				With regreasing nipple				
Terminal Block			BMC 6 Terminals								
Terminal Box Material			Cast Iron FC-200								
Additional Terminal Box			Without								
Cable Entrance	Main Size		2xM40x1.5		2xM50x1.5			2xM63x1.5			
	Plug		Plastic and Threaded Plug								
Shaft	Material		SAE 1040/45								4140
	Threaded Hole	2P	M16	M16	M20	M20	M20	M20	M20	M20	
		4 - 6P								M24	
Key			Type A				Type B				
Vibration			Level A								
Balancing			Standard Balance with 1/2 Key								
Name Plate Material			Stainless Steel AISI 304								
Painting	Plan		203A								
	Color		RAL 5009								
Electrical Features											
Design			N								
Voltage			380V with 6 Terminals								
Winding	Material		Copper								
	Impregnation		Dip and Bake				Continuous Resin Flow				
	Insulation Class		F								
Service Factor			1.25								
Rotor			Squirrel Cage Aluminum								
Thermal Protection			Thermistor 155°C Shutdown								

Note:


For features not mentioned in above table, please contact our nearest sales office.

W21 MEPS Korea IE3


Output		Frame	Full Load Torque (kgfm)	Locked Rotor Current I/ In	Locked Rotor Torque Tl/ Tn	Break-down Torque Tb/Tn	Inertia J (kgm2)	Allowable locked rotor time (s)		Weight (kg)	Sound dB(A)	Rated speed (rpm)	380 V						Full load current In (A)
								Hot	Cold				% of full load						
Efficiency													Power factor						
KW	HP	50	75	100	50	75	100												
2 Poles 3600 RPM – 60Hz																			
0.75	1	80	0.212	6.6	2.7	3.4	0.0009	20	44	16.0	62	3440	76.5	77.0	77.0	0.70	0.80	0.86	1.72
1.1	1.5	80	0.315	6.5	3.6	3.7	0.0012	15	33	20.0	62	3400	83.0	83.5	84.0	0.73	0.80	0.85	2.34
1.5	2	90L	0.421	8.5	2.9	3.6	0.0021	16	35	24.0	68	3470	84.0	85.5	85.5	0.70	0.80	0.85	3.14
2.2	3	90L	0.618	8.0	3.4	3.8	0.0025	14	31	26.0	68	3470	86.0	86.5	86.5	0.69	0.80	0.85	4.55
3	4	112M	0.830	9.5	3.1	4.5	0.0101	30	66	54.0	69	3520	86.5	88.0	88.5	0.62	0.72	0.80	6.44
3.7	5	112M	1.03	8.5	3	4.1	0.0087	28	62	48.0	69	3515	85.5	87.0	88.5	0.66	0.77	0.83	7.65
4	5.5	112M	1.11	8.4	2.4	3.6	0.0087	27	59	49.0	69	3500	88.0	88.5	88.5	0.72	0.80	0.86	7.98
5.5	7.5	132S	1.51	8.5	2.5	3.4	0.0198	27	59	62.0	72	3540	89.0	89.5	89.5	0.71	0.81	0.86	10.9
7.5	10	132S	2.07	7.7	2.5	3.5	0.0252	25	55	70.0	72	3530	89.5	90.2	90.2	0.77	0.85	0.88	14.4
11	15	160M	3.02	7.0	2.2	3.3	0.0422	25	55	109	75	3545	88.0	89.5	91.0	0.75	0.84	0.87	21.1
15	20	160M	4.12	7.8	2.3	3.7	0.0509	15	33	117	75	3545	90.3	91.0	91.0	0.75	0.83	0.86	29.1
18.5	25	160L	5.10	8.0	2	2.9	0.0565	11	24	132	75	3530	91.0	91.7	91.7	0.80	0.83	0.88	34.8
22	30	180M	6.03	8.5	2.7	3	0.0930	10	22	167	75	3555	91.0	91.7	91.7	0.78	0.84	0.87	41.9
30	40	180L	8.25	7.0	2	2.9	0.1195	16	35	196	75	3540	92.0	92.4	92.4	0.80	0.85	0.89	55.4
37	50	200L	10.1	7.0	2.6	2.8	0.2115	39	86	271	81	3560	92.5	93.0	93.0	0.77	0.84	0.87	69.5
45	60	200L	12.3	7.5	2.6	2.8	0.2331	35	77	281	81	3560	93.0	93.6	93.6	0.76	0.84	0.87	84.0
55	75	225S/M	15.1	7.0	2.5	2.6	0.3763	24	53	395	85	3555	92.5	93.6	93.6	0.82	0.86	0.89	100
75	100	250S/M	20.5	7.5	2.3	2.8	0.4366	17	37	466	85	3555	93.5	94.1	94.1	0.82	0.88	0.90	135
90	125	280S/M	24.5	8.3	2.8	3.1	1.40	46	101	788	86	3580	93.0	94.5	95.0	0.50	0.82	0.87	165
110	150	280S/M	30.0	7.6	2.4	2.8	1.36	31	68	772	86	3575	93.5	94.5	95.0	0.79	0.86	0.89	198
132	175	280S/M	36.0	7.8	2.3	2.4	1.53	26	57	822	86	3575	94.0	95.0	95.4	0.79	0.86	0.88	239
150	200	315S/M	40.9	8.1	2.4	3.2	1.88	28	62	1018	89	3575	94.0	95.4	95.4	0.80	0.87	0.90	265
160	220	315S/M	43.6	8.0	2.6	2.8	1.88	27	59	982	89	3575	95.0	95.4	95.4	0.81	0.87	0.90	283
185	250	315S/M	50.4	7.5	2.2	3	2.15	18	40	1066	89	3575	95.0	95.8	95.8	0.80	0.87	0.90	326
200	270	355M/L	54.3	9.5	3	3.1	4.09	34	75	1522	85	3585	94.2	95.4	95.8	0.85	0.89	0.91	349
4 Poles 1800 RPM – 60Hz																			
0.75	1	90S	0.416	7.2	2.0	3.1	0.0044	22	48	23.0	51	1755	83.0	83.5	83.5	0.60	0.73	0.80	1.71
1.1	1.5	90L	0.610	7.8	2.4	3	0.0060	19	42	25.0	51	1755	85.5	86.0	86.5	0.62	0.74	0.80	2.42
1.5	2	90L	0.832	8.5	2.6	3.2	0.0066	12	26	26.0	51	1755	85.5	86.5	86.5	0.59	0.70	0.78	3.38
2.2 *	3	100L	1.22	8.5	3.6	4	0.0119	25	55	40.0	54	1750	88.0	89.5	89.5	0.57	0.70	0.78	4.79
3	4	112M	1.66	7.0	2.1	3.2	0.0180	26	57	50.0	58	1755	87.5	89.0	89.5	0.60	0.71	0.78	6.53
3.7	5	112M	2.07	7.2	2.4	3.2	0.0180	23	51	50.0	58	1745	88.0	89.5	89.5	0.58	0.70	0.78	8.05
4	5.5	112M	2.23	6.8	2	2.9	0.0180	25	55	50.0	58	1750	89.0	89.5	89.5	0.62	0.74	0.80	8.49
5.5	7.5	132S	3.03	8.5	2.3	3.3	0.0527	19	42	67.0	61	1770	91.0	91.7	91.7	0.66	0.78	0.83	11.0
7.5	10	132M	4.13	8.0	2.4	3.2	0.0638	15	33	82.0	61	1770	91.0	91.7	91.7	0.67	0.79	0.84	14.8
11	15	160M	6.05	7.5	2.5	2.9	0.1071	28	62	130	69	1770	91.5	92.0	92.4	0.65	0.76	0.81	22.3
15	20	160L	8.25	7.6	3.2	3	0.1263	21	46	143	69	1770	92.5	93.0	93.0	0.64	0.75	0.80	30.6
18.5	25	180M	10.2	8.0	2.8	3.1	0.2088	26	57	188	68	1770	93.0	93.6	93.6	0.67	0.78	0.83	36.2
22 *	30	180M	12.1	7.6	2.5	3.4	0.2306	25	55	207	68	1775	92.5	93.0	93.6	0.67	0.78	0.83	43.0
30	40	200L	16.4	7.8	3.1	3.3	0.3476	24	53	264	71	1780	93.5	94.1	94.1	0.70	0.78	0.84	57.7
37	50	200L	20.2	8.5	2.7	3.5	0.4002	18	40	286	71	1780	93.5	94.5	94.5	0.66	0.77	0.82	72.5
45	60	225S/M	24.6	8.5	2.5	3	0.8822	23	51	416	75	1785	94.5	95.0	95.0	0.73	0.82	0.86	83.7
55 *	75	225S/M	30.0	8.5	2.7	3.1	1.04	21	46	466	75	1785	95.0	95.4	95.4	0.68	0.79	0.84	104
75	100	250S/M	41.0	8.5	2.8	3	1.21	13	29	522	75	1780	95.0	95.4	95.4	0.70	0.80	0.85	141
90	125	280S/M	49.1	7.9	2.4	2.9	2.10	27	59	712	80	1785	94.8	95.4	95.4	0.75	0.83	0.86	167
110	150	280S/M	60.0	7.6	2.5	3.2	2.94	39	86	884	80	1785	95.5	95.8	95.8	0.71	0.80	0.85	205
132	175	280S/M	72.0	7.8	2.5	3	3.09	24	53	874	80	1785	95.5	95.8	95.8	0.74	0.83	0.86	243
185	250	355M/L	100	8.8	2.7	3.1	8.99	63	139	1770	83	1795	95.5	96.0	96.2	0.72	0.81	0.85	344
200	270	355M/L	109	7.0	2	2.4	7.55	63	139	1583	83	1790	95.5	96.2	96.2	0.75	0.83	0.86	367
6 Poles 1200 RPM – 60Hz																			
0.75	1	100L	0.632	5.5	2.2	2.8	0.0132	102	224	35.0	53	1155	82.0	82.5	82.5	0.51	0.64	0.71	1.95
1.5	2	112M	1.25	7.6	3	3.3	0.0257	44	97	50.0	52	1170	86.5	88.5	88.5	0.47	0.60	0.67	3.84
2.2	3	132S	1.82	6.6	1.8	2.5	0.0530	100	220	67.0	55	1175	88.5	89.5	89.5	0.49	0.62	0.70	5.34
3.7	5	132S	3.08	6.8	2.2	2.5	0.0568	48	106	69.0	55	1170	89.0	89.5	89.5	0.52	0.65	0.72	8.72
5.5 *	7.5	132M	4.58	7.6	2.3	3	0.0757	35	77	92.0	55	1170	90.5	91.0	91.0	0.52	0.65	0.72	12.8
7.5	10	160M	6.22	7.0	2.4	3	0.1615	26	57	128	59	1175	90.5	91.0	91.0	0.64	0.76	0.82	15.3
11	15	160L	9.12	7.6	3	3.5	0.1895	17	37	143	59	1175	90.0	91.7	91.7	0.58	0.71	0.78	23.4
15	20	180M	12.4	9.5	2.7	3.2	0.3111	15	33	184	59	1175	91.0	91.7	91.7	0.73	0.83	0.87	28.6
18.5 *	25	180L	15.3	9.6	3.2	3.5	0.4193	15	33	225	59	1175	92.5	93.0	93.0	0.73	0.83	0.87	34.7
22	30	200L	18.2	6.5	2.4	3	0.4914	31	68	271	62	1180	92.7	93.0	93.0	0.68	0.79	0.83	43.3
30	40	225S/M	24.6	8.0	2.5	3.4	1.24	41	90	419	65	1190	92.8	94.1	94.1	0.67	0.78	0.83	58.4
37	50	225S/M	30.3	8.4	2.6	3.6	1.34	31	68	434	65	1190	92.9	94.0	94.1	0.65	0.77	0.82	72.9
45 *	60	225S/M	36.8	8.5	2.8	3	1.43	23	51	461	65	1190	93.4	94.5	94.5	0.68	0.79	0.83	87.2
55 *	75	250S/M	45.2	7.0	2.5	3	1.80	29	64	549	65	1185	94.0	94.5	94.5	0.75	0.833		

Dimensional

FRAME 80-200



FRAME 225-355



Frame	A	AA	AB	AC	AD	B	BA	BB	C	H	HA	HC	HD	K	L	S1	Bearing			
																	DE	NDE		
80	125	35	149	159	136	100	40	1256	50	80	13	157	216	10	286	2xM20x1.5	6205-ZZ	6203-ZZ		
90S	140	38	164	179	155	100	42	131	56	90	15	177	245		304	2xM25x1.5	6205-ZZ	6204-ZZ		
90L						125		156					217		329					
100L	160	49	188	199	165	140	50	173	63	100	16	198	265	12	376/*410	2xM32x1.5	6206-ZZ	6205-ZZ		
112M	190	48	220	222	184			177	70	112	18.5	235	296		393		6307-ZZ	6206-ZZ		
132S	216	51	248	270	212			178	225	89	132	20	274		344		452	2xM40x1.5	6309-C3	6209-Z-C3
132M						490/*520														
160M	254	64	308	312	255	210	65	254	108	160	22	317	415	14.5	598	2xM40x1.5	6311-C3	6211-Z-C3		
160L						254		298							642					
180M	279	80	350	358	275	241	75	294	121	180	28	360	455		664/*690				6312-C3	6212-Z-C3
180L						279		322							702/*730					
200L	318	82	385	396	305	305	85	370	133	200	30	402	500	18.5	767	2xM50x1.5	6314-C3	6314-C3		
225S/M	356	80	436	476	374	286	105	391	149	225	34	466	598		817					
250S/M	406	100	506			311									847/*900					
280S/M	457	100	557	600	468	349	138	449	168	250	42	491	623	24	923/*977	2xM63x1.5	6314-C3	6314-C3		
315S/M	508	120	628			368									1036					
315L	508	120	630			419									1126		6316-C3	6316-C3		
355M/L	610	140	750	816	685	406	152	558	216	315	52	613	812	28	1156		6319-C3	6316-C3		
						457									1353		6314-C3	6314-C3		
						560									1383		6319-C3	6316-C3		
						630	200	760	254	355	50	725	1040		1396		6316-C3	6314-C3		
															1466		6322-C3	6319-C3		

Frame	D	E	ES	F	G	GD	Frame	D	E	ES	F	G	GD
80	19j6	40	28	6	15.5	6	225S/M	55m6	110	100	16	49	10
90S	24j6	50	36	8	20	7		60m6	140	125	18	53	11
90L	24j6	50	36	8	20	7	250S/M	60m6	140	125	18	58	11
100L	28j6	60	45	8	24	7		65m6	140	125	18	58	11
112M	28j6	60	45	8	24	7	280S/M	65m6	140	125	18	58	11
132S	38k6	80	63	10	33	8		75m6	140	125	20	67.5	12
132M	38k6	80	63	10	33	8	315S/M	65m6	140	125	18	58	11
160M	42k6	110	80	12	37	8		80m6	170	160	22	71	14
160L	42k6	110	80	12	37	8	315L	65m6	140	125	18	58	11
180M	48k6	110	80	14	42.5	9		80m6	170	160	22	71	14
180L	48k6	110	80	14	42.5	9	355M/L	75m6	140	125	20	67.5	12
200L	55m6	110	80	16	49	10		100m6	210	200	28	90	16

* Designs with extended non-drive end shield:					
kW	Poles	Frame	kW	Poles	Frame
2.2	4	100L*	55	4	225S/M*
3	4	112M*	5.5	6	132M*
3.7	4	112M*	18.5	6	180L*
4	4	112M*	45	6	225S/M*
22	4	180M*	55	6	250S/M*


Notes:

- * The value with (*) in front are motors which are with extended end shield.
- All dimensions are in millimeters.
- Larger and smaller flanges on request.
- The data for frame 355M/L shown above are for horizontal mounting applications under standard coupling loads. The customer must inform when application is vertical or under special coupling loads.
- The values shown are subject to change without prior notice.
- To obtain guaranteed values please contact our nearest sales office.

Flange Dimensions

“FF” Flange


IEC Frame	"FF" Flange									N° of Holes
	Flange	C	LA	M	N	P	T	S	α	
63	FF-115	40	9	115	95	140	3	10	45°	4
71	FF-130	45		130	110	160	3.5			
80	FF-165	50	10	165	130	200		12		
90S/L		56								
100L	FF-215	63	11	215	180	250	4	15		
112M		70								
132S/M	FF-265	89	12	265	230	300	5	19		
160M/L	FF-300	108	18	300	250	350				
180WL		121								
200M/L	FF-350	133		350	300	400				
225S/M	FF-400	149		400	350	450				
250S/M	FF-500	168		500	450	550				
280S/M		190								
315S/M	FF-600	216	22	600	550	660	6	24	22°30'	8
355 M/L	FF-740	254		740	680	800				



Standard Frame

“C” Din Flange

IEC Frame	"C" DIN Flange							N° of Holes
	Flange	C	M	N	P	S	T	
63	C-90	40	75	60	90	M5	2.5	4
71	C-105	45	85	70	105	M6		
80	C-120	50	100	80	120		M8	
90S/L	C-140	56	115	95	140	M8		
100L	C-160	63	130	110	160			
112M		70						
132S/M	C-200	89	165	130	200	M10		



Standard Frame



WEG Worldwide Operations

ARGENTINA

San Francisco - Cordoba
Phone: +54 3564 421484
info-ar@weg.net

Cordoba - Cordoba
Phone: +54 3514 641366
weg-morbe@weg.com.ar

Buenos Aires
Phone: +54 1142 998000
ventas@pulverlux.com.ar

AUSTRALIA

Scoresby - Victoria
Phone: +61 3 97654600
info-au@weg.net

AUSTRIA *

Markt Piesting - Wiener
Neustadt-Land
Phone: +43 2 633 4040
watt@wattdrive.com

Vienna
Phone: +43 1 796 2048
wtr@weg.net

BELGIUM *

Nivelles - Belgium
Phone: +32 67 888420
info-be@weg.net

BRAZIL

Jaraguá do Sul - Santa Catarina
Phone: +55 47 32764000
info-br@weg.net

CHILE

La Reina - Santiago
Phone: +56 2 27848900
info-cl@weg.net

CHINA

Nantong - Jiangsu
Phone: +86 513 85989333
info-cn@weg.net

Changzhou - Jiangsu
Phone: +86 519 88067692
info-cn@weg.net

Rugao - Jiangsu
Phone: +86 513 80672011
zhuhua@weg.net

COLOMBIA

San Cayetano - Bogota
Phone: +57 1 4160166
info-co@weg.net

Sabaneta - Antioquia
Phone: +57 4 4449277
info-co@weg.net

ECUADOR

El Batan - Quito
Phone: +593 2 5144339
wegecuador@weg.net

FRANCE *

Saint-Quentin-Fallavier - Isère
Phone: +33 4 74991135
info-fr@weg.net

GERMANY *

Türnich - Kerpen
Phone: +49 2237 92910
info-de@weg.net

Balingen - Baden-Württemberg
Phone: +49 7433 90410
info@weg-antriebe.de

Homburg (Efze) - Hesse
Phone: +49 5681 99520
info@akh-antriebstechnik.de

GHANA

Accra
Phone: +233 30 2766490
ghana@zestweg.com

INDIA

Bangalore - Karnataka
Phone: +91 080 46437450
info-in@weg.net

Hosur - Tamil Nadu
Phone: +91 4344 301577
info-in@weg.net

ITALY *

Cinisello Balsamo - Milano
Phone: +39 2 61293535
info-it@weg.net

JAPAN

Yokohama - Kanagawa
Phone: +81 45 5503030
info-jp@weg.net

MALAYSIA

Shah Alam - Selangor
Phone: +60 3 78591626
info@wattdrive.com.my

MEXICO

Huehuetoca - Mexico
Phone: +52 55 53214275
info-mx@weg.net

Tizayuca - Hidalgo
Phone: +52 77 97963790
info-mx@weg.net

NETHERLANDS *

Oldenzaal - Overijssel
Phone: +31 541 571080
info-nl@weg.net

PERU

La Victoria - Lima
Phone: +51 1 2097600
info-pe@weg.net

PORTUGAL *

Maia - Porto
Phone: +351 22 9477700
info-pt@weg.net

RUSSIA and CIS *

Saint Petersburg
Phone: +7 812 363 2172
sales-wes@weg.net

SOUTH AFRICA

Johannesburg
Phone: +27 (0) 11 7236000
info@zestweg.com

Cape Town
Phone: +27 (0) 21 507 7200
gentsets@zestweg.com

Heidelberg
Phone: +27 (0) 16 349 2683/4/5
wta@zestweg.com

SPAIN *

Coslada - Madrid
Phone: +34 91 6553008
info-es@weg.net

Valencia
Phone: +34 96 1379296
info@autrial.es

SINGAPORE

Singapore
Phone: +65 68589081
info-sg@weg.net

Singapore
Phone: +65 68622220
info-sg@weg.net

SCANDINAVIA *

Mölnlycke - Sweden
Phone: +46 31 888000
info-se@weg.net

UK *

Redditch - Worcestershire
Phone: +44 1527 513800
info-uk@weg.net

UNITED ARAB EMIRATES

Jebel Ali - Dubai
Phone: +971 4 8130800
info-ae@weg.net

USA

Duluth - Georgia
Phone: +1 678 2492000
info-us@weg.net

Bluffton - Indiana
Phone: +1 800 5798527
info-us@weg.net

Minneapolis - Minnesota
Phone: +1 612 3788000
info-us@weg.net

Washington - Missouri
Phone: +1 636-239-9300
wegwill@weg.net

VENEZUELA

Valencia - Carabobo
Phone: +58 241 8210582
info-ve@weg.net

For those countries where there is not a WEG own operation, find our local distributor at www.weg.net.



WEG(Nantong) Electric Motor Mfg. Co.,Ltd
#128, Xinkai South Road, NETDA, Jiangsu, China
Tel: +86-513-85989333
Fax: +86-513-85922162
info-cn@weg.net
www.weg.net