

WRAPX® EVD 47

PRODUCT DESCRIPTION

Two-component polyurea-based elastomeric primer/finish, high-build. Low VOC. Flexible coating with excellent anticorrosive and abrasion resistance.

RECOMMENDED USE

Used on flanges, valves of all diameters, and screw seals; can be applied over W-LUBI DSR 473 protective wax film to allow easy removal when maintenance access is needed.

CERTIFICATIONS AND APPROVALS

When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.

PACKAGING

Component A	3.6L Package containing 3.6L 20L Package containing 20L
Component B	3.6L Package containing 3.6L 20L Package containing 20L

CHARACTERISTICS

Color	Gray.
Gloss	Semi-Matte
Volume Solids	99 ± 1% (ISO 3233)
Dry Film Thickness	500 µm - 2.000 µm
Dry Heat Resistance	Maximum temperature 120 °C. The product maintains its chemical properties up to a temperature of 120 °C, but from 60°C, color and gloss variations in the paint may occur.
Theoretical Coverage	without dilution at a dry film thickness of 1.250 µm. Loss factors during application are not considered.

DRYING

Drying

	10 °C	25 °C	35 °C
Toque	2 horas	40 min	30 min
Manuseio	5 horas	2 horas	90 min
Final	5 dias	5 dias	5 dias

Topcoat Recoat Drying

	10 °C	25 °C	35 °C
Minima	6 horas	4 horas	3 horas
Maxima	20 horas	16 horas	12 horas

SURFACE PREPARATION

Standard Surface Preparation

The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

Remove accumulated dirt using a dry brush, clean dry cloth, compressed air blow, vacuum, or a combination of these. Remove soluble salts by washing with plenty of fresh water, preferably under low pressure (up to 5,000 psi), according to SSPC-SP12/NACE No. 5 standard.

The WRAPX® coating must be applied over W-LUBI DSR 473 for release function. Other waxy or oily release agents must only be used with prior evaluation by the WEG Technical Department.

Over Primer

The product must be applied over a specific primer. The primer must be clean, dry, and free of contaminants. The topcoat must be applied within the primer recoat interval. Consult the primer technical bulletin for correct application.

Respect the product recoat interval. If exceeded, perform light manual/mechanical sanding to break gloss and clean dust/residues for better adhesion between coats.

APPLICATION PREPARATION

Mixing	Homogenize the content of component B using mechanical or pneumatic stirring. Ensure no sediment remains at the bottom of the container. To avoid bubble formation, stirring is not recommended for component A.
Mixing Ratio	By volume: 1 A x 1 B.
Thinner	Not applicable.
Dilution	Ready to use.
Notes	No dilution is required. Product ready to use. If necessary, consult the WEG Technical Department.
Pot Life	2 min The shelf life of the mixture is reduced as the ambient temperature increases. The pot-life test of the mixture is carried out according to ABNT NBR 15742; however, different volumes of paint prepared at once, combined with varying ambient and paint temperatures, will affect the mixture's shelf life, potentially resulting in outcomes different from those stated in this technical bulletin.
Induction Time	No induction time required. In very hot locations, we recommend consulting WEG's Technical Department.

APPLICATION METHODS

Airless Spray Gun	Airless: Plural Component Sprayer (250.150.2) Fluid pressure: 1900 - 2500 psi Hose: 3/16" inner diameter.
Cleaning of the equipments:	Not applicable.
Notes	The data presented serves as a guide and similar equipment may be used. Changes in pressures and nozzle sizes may be necessary to improve spraying characteristics. Purge the compressed air line to avoid paint contamination. Before application, ensure that the equipment and respective components are clean and in optimal condition. Do not leave material in hoses, guns, or equipment used for spraying. Thoroughly wash all used equipment.

APPLICATION PERFORMANCE

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

For optimal application properties, the paint temperature should be between 21°C and 27°C before mixing and application.

Substrate temperature, climatic and environmental conditions during application and curing, as well as applied film thickness, may affect drying time.

Painting is recommended only if the surface temperature is at least 3°C above the dew point and maximum temperature of 60°C. For different application temperatures, consult WEG Technical Department.

This product has low resistance to exposure to sunlight. When exposed to weathering, the applied film will show loss of color and gloss over time. The film is not impaired regarding anticorrosive protection.

Must not be applied under adverse conditions, such as relative humidity (RH) above 85%, as color

and appearance changes may occur.

On freshly painted surfaces in direct contact with water during the curing process, localized staining with color change (more visible in darker colors), curing delay, and compromised product performance may occur.

Product not recommended for internal tank painting.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: www.weg.net.

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.

Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.

Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.

The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.