











Data Sheet



CLEARCOAT UHT W-60

	Product Description	2K HS hydroxylated acrylic clearcoat for finishes with excellent leveling and image distinction, compatible for application with solvent-based and water-based lines. Recommended for general painting, partial painting and repainting of motor vehicles	
		Useful life 3 years	
	Performance		6 - 8 m ² /L 50 a 60 µm
	Mixing Ratio	2 Parts of A 1 Part of B	
		Pot life 2 hours	
	Hardener	Temperature below 15°C - UHT 5561 hardener low temperature Ambient temperature 25°C - UHT 5560 intermediate hardener	
	Thinner	Temperature below 15°C - Thinner 5860 low temperature Ambient temperature 25°C - Thinner 5870 intermediate Average temperature 30°C - Thinner 5880 high temperature Ambient temperature 25°C high quality: PU Thinner 5890 Dilution 10 - 20%	
	Application Viscosity	13 – 17s Copo FORD 4 25° C 77°F 16 – 19s Copo DIN 4 25° C 77°F	
	Application Gun	1,2 – 1,5 mm	2 - 3 BAR / 30 - 45 PSI
	Evaporation at 25°C 77°F	5 - 10 minutes	
	Number of passes	2 passes	1 pass = 25 a 30 micra
	Drying at 10°C 50°F	Touch 15 minutes Pressure 40 minutes Polishing 24 hours	
	Drying at 25°C 77°F	Touch 10 minutes Pressure 30 minutes Polishing 24 hours	
	Drying at 60°C 140°F	Polishing 30 minutes	
	Shortwave infrared	30 minutes a 1 m.	

- Perform a good degreasing to clean the part to be repainted
- Avoid excessive thicknesses
- Clean application equipment with acrylic/polyurethane thinners;
- It is recommended to polish within 24 hours;
- Use hardener and thinner as recommended;
- Always use the WEG product and complement set.