

EXPLOSION PROOF MOTORS

1/3 - 500 HP
2, 4, 6, & 8 Pole


Motors

Automation

Energy

Transmission and
Distribution

Coatings




Explosion Proof - Three Phase

Three Phase

Foot Mount and Flange Mount

WEG Explosion Proof motors are suitable for applications requiring UL or CSA certification for hazardous locations. Thermally protected with thermostats, all motors manufactured are submitted to routine testing at the factory to ensure compliance to the required specifications. WEG Explosion Proof motors are specifically designed to meet or exceed all North American requirements for energy efficiency.



Standard Features:

- Efficiency Certification number CC029A according to US Department of Energy Regulations
- Three-phase, 60Hz
- Voltage: 208-230/460, 460 or 575V
- Squirrel cage rotor / Aluminum die cast
- Totally Enclosed Fan Cooled – TEFC (IP54 & IP55)
- Ball bearings are supplied as standard regreasable bearings 254T Frames & Larger
- Cast iron frame
- Class 'F' insulation
- Temperature rise: Class 'B' (80°C) FL
- Service factor: 1.15
- Inverter Duty
- NEMA dimensions
- NEMA ratings design 'B'
- Continuous Duty (S1)
- 55° ambient @ 1.0SF through 150hp 2 and 4 pole
- 104°F (40°C) ambient temperature
- Altitude: 3300 ft (1000 m)
- 1045 Carbon Steel Shaft for frames up to 365T
- 4140 steel shaft for motors 404T and above.
- Class 'F' insulation for all frames
- 60/50Hz Nameplate
- Stainless steel nameplate
- Paint: Epoxy with Polyurethane top coat (exceeds ASTM B117 salt spray test 200 hours)
- Color: RAL 5009 – Blue
- NPT threaded terminal box
- Non-sparking fan
- Thermostats
- F1 mount

Optional Features:

- Flange mount
- AEGIS® inside
- Special voltages
- Space heaters
- Specially dimensioned shaft
- Double shaft
- Stainless steel shaft
- Footless
- Other mounting configurations
- IP66
- Encoders
- TENV

Applications:

- Petro Chem
- Flour / feed mills
- Grain elevators
- Fans
- Pumps
- Blowers
- Material handling equipment
- Other applications requiring motors UL or CSA listed for hazardous locations

CSA AND UL APPROVED
CSA approved - File LR 50962
Class I, Division I, groups C and D
Class II, Division I, groups F and G

IEC - Ex Certification Available

UL approved - File E 87848
Temperature code T3C
Frame 143T up to 326T
Class I, Division I, groups C and D
Class II, Division I, groups F and G

Frame 364T up to 586/7
Temperature code T3C
Class I, Division I, groups C and D
Class II, Division I, groups F and G*
* For group G, Service Factor 1.0




Fractional Explosion Proof - Three Phase

Great complement to our integral explosion proof offering, allowing us to come to customers with complete solution.

Standard Features:

- Class F insulation
- 50°C ambient temperature rating
- 1.0 service factor
- Foot mount motors with and without C-flange
- IP 55 rating
- Class I - Group C & D and Class II - Groups E, F & G – T3B
- Thermally Protected
- Three-Phase motors also rated for 50Hz
- Long leads for remote wiring
- Unassembled aluminum conduit box included
- Aluminum endshields



Single-Phase motors

2-Pole - from 1/3HP to 2HP
4-Pole – from 1/3HP to 1.5HP
1/3HP 4-Pole is TENV
All others are TEFC

Three-Phase motors

2-Pole - from 1/3HP to 2HP
4-Pole – from 1/3HP to 2HP
1/3HP 2 & 4-Pole are TENV
All others are TEFC

Now available in Jet Pump 56J


Single-Phase motors

2-Pole - from 1/2HP to 1.5HP
TEFC

Three-Phase motors

2-Pole - from 1/2HP to 2HP
TEFC





WEG's scope of solutions is not limited to
the products and solutions presented in
this brochure.

**Contact WEG for information on additional
products and solutions.**


**For WEG's worldwide
operations visit our website**



www.weg.net



 **1-800-ASK-4WEG**

 **info-us@weg.net**

 **Duluth, GA**

US.Expllosion.Proof.2022

Information contained herein is subject to change
without notice.