

**W-LACK ADA 12**

**PRODUCT DESCRIPTION**

Alkyd resin-based topcoat with anti-slip properties.  
 Good weather resistance properties. Forms a highly textured film, thereby offering anti-slip properties.

**RECOMMENDED USE**

Used in industrial floors, stairs, walkways, ramps, ship decks, and light traffic areas in general.

**CERTIFICATIONS AND APPROVALS**

When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.

**PACKAGING**

<b>Component A</b>	3.6L Package containing 3.6L
--------------------	------------------------------

**CHARACTERISTICS**

<b>Color</b>	Gray. Green. Colors upon request.
<b>Gloss</b>	Matte
<b>VOC content</b>	313.77 g/l
<b>Volume Solids</b>	62 ± 2% (ISO 3233)
<b>Shelf Life</b>	12 months
<b>Dry Film Thickness</b>	35 µm - 45 µm
<b>Dry Heat Resistance</b>	Maximum temperature 60 °C. The product maintains its chemical properties up to a temperature of 60 °C, but from 60°C, color and gloss variations in the paint may occur.
<b>Theoretical Coverage</b>	15,50 m <sup>2</sup> /l without dilution at a dry film thickness of 40 µm. Loss factors during application are not considered.

**DRYING**

<b>Drying</b>	<b>25 °C</b>
<b>Touch</b>	3 hours
<b>Manipulation</b>	24 hours
<b>Final</b>	72 hours
 <b>Recoat Drying</b>	<b>25 °C</b>
<b>Minimum</b>	5 hours
<b>Maximum</b>	24 hours

**SURFACE PREPARATION**

**Standard Surface Preparation**  
 The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

The surface must be clean, dry, and free of contaminants. Completely remove oils, greases, and fats according to SSPC-SP1.

If the maximum interval indicated for applying the subsequent coat is exceeded, it is necessary to proceed with surface sanding to obtain adhesion between layers.

Accumulated dirt must be removed using a dry brush, and soluble salts must be removed by washing with fresh water under high pressure.



**Over Primer**

The product must be applied over a specific primer. The primer must be clean, dry, and free of contaminants. The topcoat must be applied within the primer recoat interval. Consult the primer technical bulletin for correct application.

Respect the product recoat interval. If exceeded, perform light manual/mechanical sanding to break gloss and clean dust/residues for better adhesion between coats.

Weglack ADA 124 must be applied over a specific primer in order to form a proper coating system. For the correct application of the primer, consult its technical data sheet.

**APPLICATION PREPARATION**

<b>Mixing</b>	Homogenize the content of the container using mechanical or pneumatic stirring. Ensure no sediment remains at the bottom of the container.
<b>Thinner</b>	RAZ SOLVENT
<b>Dilution</b>	Depending on the application method, dilute to a maximum of 5%.
<b>Notes</b>	The amount of Diluent may vary depending on the type of equipment used and environmental conditions during application. Only add Diluent after complete mixing of the other components. Do not dilute with solvents not allowed by local legislation, and do not exceed the indicated dilution percentage. Excessive dilution may affect film formation, appearance, and make it difficult to achieve the specified thickness.
<b>Pot Life</b>	Not relevant.

**APPLICATION METHODS**

<b>Conventional Spray Gun</b>	Spray gun: Not recommended.
<b>Airless Spray Gun</b>	Airless: not recommended.
<b>Roller</b>	Use a short-haired, seamless wool or synthetic roller for epoxy paints. The finish granularity must be controlled during application.
<b>Brush</b>	Recommended only for small area touch-ups or "stripe coat" (screws, nuts, weld beads, sharp corners, and touch-ups).
<b>Cleaning of the equipments:</b>	RAZ SOLVENT
<b>Notes</b>	The data presented serves as a guide and similar equipment may be used. Before application, ensure that the equipment and respective components are clean and in optimal condition. Reinforce all sharp corners, gaps, and weld beads with a brush to avoid premature failures in these areas. Clean all equipment immediately after use.

**APPLICATION PERFORMANCE**

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

Must not be applied on condensed surfaces.

For optimal application properties, the paint temperature should be between 21°C and 27°C before mixing and application.

Painting is recommended only if surface temperature is at least 3°C above the dew point.

Substrate temperature, climatic and environmental conditions during application and curing, as well as applied film thickness, may affect drying time.

Must not be applied under adverse conditions, such as relative humidity (RH) above 85%, as color and appearance changes may occur.



Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

---

**SYSTEM COMPATIBILITY AND MAINTENANCE REPAINTING**

The primer repainting interval must be respected for the application of the topcoat. If the maximum interval indicated is exceeded, manual/mechanical sanding with sandpaper to remove gloss is necessary. The primer surface must be dry and free of contaminants.

In situations where the nature of the primer is unknown, it is recommended to test the product's compatibility on a small area; it must be ensured that the original material is well adhered. All non-adhered paint must be removed; areas with corrosion or applications over aged paints must be treated according to technical guidance.

Direct application of the product over zinc-rich primers based on ethyl silicate, alkyd primers, coal tar-based paints, and other single-component primers is not recommended. When topcoat application over any of the above primers is required, we recommend applying a suitable intermediate product.

---

**SAFETY PRECAUTIONS**

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: [www.weg.net](http://www.weg.net).

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.

Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

---

**NOTE**

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.

Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.

The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.