

## W-LACK HPP 12

### PRODUCT DESCRIPTION

High-performance phenolated alkyd resin primer, fast-drying. Contains zinc phosphate corrosion-inhibiting pigmentation.

### RECOMMENDED USE

Provides excellent adhesion and anticorrosive protection on phosphated or degreased carbon steel. Recommended for painting machinery, equipment, agricultural implements, and metal structures.

### CERTIFICATIONS AND APPROVALS

When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.

### PACKAGING

#### Single Component

0.95 US gal Package containing 0.95 US gal  
5.28 US gal Package containing 5.28 US gal  
52.83 US gal Package containing 52.83 US gal

### CHARACTERISTICS

|                             |                                                                                                                                                                                |
|-----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Color</b>                | According to customer standard.<br>RAL and Munsell chart.                                                                                                                      |
| <b>Gloss</b>                | Semi-Matte                                                                                                                                                                     |
| <b>VOC content</b>          | 3.91 lb/gal                                                                                                                                                                    |
| <b>Volume Solids</b>        | 40 ± 5% (ISO 3233)                                                                                                                                                             |
| <b>Shelf Life</b>           | 12 months                                                                                                                                                                      |
| <b>Dry Film Thickness</b>   | 1.2 mils - 1.6 mils                                                                                                                                                            |
| <b>Dry Heat Resistance</b>  | Maximum temperature 140 °F.<br>The product maintains its chemical properties up to a temperature of 140 °F, but from 140°F, color and gloss variations in the paint may occur. |
| <b>Theoretical Coverage</b> | 465.8 ft²/gal without dilution at a dry film thickness of 1.4 mils. Loss factors during application are not considered.                                                        |

### DRYING

**77 °F**

|                                    |        |
|------------------------------------|--------|
| <b>Touch Dry:</b>                  | 40 min |
| <b>Handle Dry:</b>                 | 11 h   |
| <b>Full Cure:</b>                  | 3 days |
| <b>Minimum recoat drying time:</b> | 5 h    |
| <b>Maximum recoat drying time:</b> | 24 h   |

### SURFACE PREPARATION

#### Standard Surface Preparation

The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

Remove accumulated dirt using a dry brush, clean dry cloth, compressed air blow, vacuum, or a combination of these. Soluble salts must be removed by washing with plenty of fresh water.

Remove accumulated dirt using a dry brush, clean dry cloth, compressed air blow, vacuum, or a combination of these. Remove soluble salts by washing with plenty of fresh water, preferably under low pressure (up to 5,000 psi), according to SSPC-SP12/NACE No. 5 standard.

#### Degreasing

Completely remove oils and greases by applying a degreasing product or according to the solvent cleaning method. Whenever cleaning surfaces with cloths, replace them to avoid saturation. Do not



use cotton waste or colored cloths.

## Maintenance and Repair

NOTE: Respect the recoating interval for subsequent coat application. If exceeded, perform light manual/mechanical sanding to break the previous coat gloss, followed by dust and residue cleaning to ensure better adhesion between paint layers.

## Carbon Steel Surfaces

Hard surface layers (e.g., layers resulting from flame cutting) must be removed by grinding before starting abrasive blasting.

All welds must be inspected and, if necessary, repaired before completing abrasive blasting. Porosities, cavities, weld splatter, etc., must be repaired with proper mechanical treatment or welding repair. In other areas, round edges and sharp corners (r e 0.0787 in, ISO 8501-3).

## APPLICATION PREPARATION

|                 |                                                                                                                                                                                                                                                                                                                                                                                                                                |
|-----------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Mixing</b>   | Homogenize the content of the container using mechanical or pneumatic stirring. Ensure no sediment remains at the bottom of the container.                                                                                                                                                                                                                                                                                     |
| <b>Thinner</b>  | ALKYDIC DILUENT 1024                                                                                                                                                                                                                                                                                                                                                                                                           |
| <b>Dilution</b> | Depending on the application method, dilute to a maximum of 25%.                                                                                                                                                                                                                                                                                                                                                               |
| <b>Notes</b>    | The amount of Diluent may vary depending on the type of equipment used and environmental conditions during application. Only add Diluent after complete mixing of the other components. Do not dilute with solvents not allowed by local legislation, and do not exceed the indicated dilution percentage. Excessive dilution may affect film formation, appearance, and make it difficult to achieve the specified thickness. |
| <b>Pot Life</b> | Not relevant.                                                                                                                                                                                                                                                                                                                                                                                                                  |

## APPLICATION METHODS

|                                    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
|------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Airless Spray Gun</b>           | Airless: Use minimum pump 60:1<br>Fluid pressure: 1500 - 2500 psi<br>Hose: 1/4" inner diameter<br>Nozzle: 0.013" - 0.017".                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| <b>Roller</b>                      | Not recommended.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| <b>Brush</b>                       | Recommended only for small area touch-ups or "stripe coat" (screws, nuts, weld beads, sharp corners, and touch-ups).                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| <b>Cleaning of the equipments:</b> | ALKYDIC DILUENT 1024                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| <b>Notes</b>                       | The data presented serves as a guide and similar equipment may be used.<br>Changes in pressures and nozzle sizes may be necessary to improve spraying characteristics. Purge the compressed air line to avoid paint contamination.<br>Before application, ensure that the equipment and respective components are clean and in optimal condition.<br>In spray application, overlap each gun pass by 50%, finishing with a cross pass. This technique avoids uncovered or unprotected areas and ensures proper aesthetic finish.<br>Reinforce all sharp corners, gaps, and weld beads with a brush to avoid premature failures in these areas.<br>Clean all equipment immediately after use.<br>Do not leave material in hoses, guns, or equipment used for spraying. Thoroughly wash all used equipment.<br>It is considered good practice to periodically wash the spraying equipment during the day. The cleaning frequency depends on the amount sprayed, temperature, and elapsed time, including all delays. |

## APPLICATION PERFORMANCE



For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

Light colors may require more than one coat to achieve uniform coverage.

For optimal application properties, the paint temperature must be between 69.8°F - 80.6°F before mixing and application.

Before application, observe weather conditions: there must be no threat of rain or drizzle. Surface temperature must be at least 37.4°F above the dew point, and relative humidity should not exceed 85%. Adverse conditions may cause color variations and other characteristics. Consult WEG Technical Department.

We recommend painting only if the measured surface temperature is at least 5.4°F above the dew point.

Substrate temperature, climatic and environmental conditions during application and curing, as well as applied film thickness, may affect drying time.

Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

Under adverse weather conditions in indoor and/or outdoor environments with high relative humidity, rain or drizzle, low or very low temperatures, and excessively high temperatures, variations in color and other product characteristics may occur. Please consult WEG's Technical Department for more information.

---

## SYSTEM COMPATIBILITY AND MAINTENANCE REPAINTING

The primer repainting interval must be respected for the application of the topcoat. If the maximum interval indicated is exceeded, manual/mechanical sanding with sandpaper to remove gloss is necessary. The primer surface must be dry and free of contaminants.

---

## SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: [www.weg.net](http://www.weg.net).

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.

Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

---

## NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.

Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.

The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.

---