

# PLC – PLC410 Programmable Logic Controller

**Power** in  
processing,  
**flexibility** in  
programming

Industrial Motors

Commercial &  
Appliance Motors

**Automation**

Digital &  
Systems

Energy

Transmission &  
Distribution

Coatings



Driving efficiency and sustainability





# S U M M A R Y

## **PLC410**

---

04

## **Introduction**

---

04

## **Highlights**

---

05

## **Characteristics**

---

06

## **Connectivity**

---

10

## **Specifications**

---

13

## **Dimensions**

---


14

## **Expansion Modules**

---

15







## Power in processing, flexibility in programming

The **PLC410** is a **Medium-sized Programmable Logic Controller**, compact in size, robust in performance and modular in programming. It is a solution that carries WEG's technology and the flexibility of the CODESYS® platform, enabling the development of flexible and efficient solutions.

With high-performance hardware, it is possible to perform highly complex tasks, such as timing, counting, basic and advanced math operations, interlocking logic, PID control and much more. All that, at high speed and with maximum operational accuracy.





PROCESS

CONTROL

COMMUNICATION

MONITORING

CONNECTIVITY

ENGINEERING


## Highlights




Develop your solutions on the CODESYS® platform



Get the best performance through powerful hardware



Compact design



Expandable Modular Design




Easily add new Plug & Play expansions



Add up to 8 expansion modules locally




Reuse your programs through the object-oriented programming concept



WEG IoT Ready



# Perform complex tasks with high performance processing



# Perform complex tasks with high performance processing

Developed to be a high-performance, mid-sized controller with built-in IIoT resources, the PLC410 allows you to obtain maximum results from your applications, optimizing time and increasing your productive and operational efficiency. Flexibility is another unique feature of this solution, enabling numerous protocols available in a single product, without the need for additional communication modules.

## Features

### Integrated connectivity and IIoT

Native IIoT protocols and services:

- Web Client SL
- MQTT Client SL
- Mail Service SL
- SMS Service SL
- SNMP Service SL
- Supported SNMP Versions
- SNTIP Service SL
- AWS IoT Core Client SL
- Azure IoT Hub Client SL
- JSON Web Token SL
- Web Socket Client SL

### MicroSD card slot

Maximum capacity up to 2 TB.

### Mini USB device port

1x mini USB Device Port for programming and monitoring via PC.


### Hardware and software in harmony

CODESYS® solution development platform, greater operational stability and smart tools.



### Industrial ports and protocols

1x Ethernet Port 10/100 Mbits (EtherNet/IP-Scanner/Adapter, Modbus TCP Client/Server and EtherCAT-Client), 1x CAN Port (CANopen-Master) and 1x RS485 (Modbus RTU Master/ Slave). Allows integration to the main industrial communication networks.



### Status LEDs

Visual status indication.

# Have more flexibility to develop your automation

The PLC410 Programmable Controller was developed on a platform that allows the interchangeability of the MOD expansion modules used in the RUW200 lines and in the PLC500 line. That provides high flexibility and synergy between our product line, all of which following the Plug & Play concept.

### Complete line of expansions

The same expansion boards used in the RUW200 remote units and PLC500 can be used in the PLC410.

### Expansion boards with numerous possibilities:

- Thermocouple (J, K and T)
- RTD (Pt100 and Pt1000)
- Load cell
- Relay output
- Digital inputs and outputs
- Analog inputs and outputs

### Expansion port cover


Isolates the contacts from the external environment, increasing the connection's durability.

### Quick connectors

Power supply, inputs and outputs.

### Greater savings with a space-efficient installation


Expansion modules less than 1 inch wide.




To learn more, access or [click here.](#)

# Increase your productivity with flexibility and high performance

## Connectivity





In the era of Industry 4.0, where productive flexibility, adaptability, big data and cloud computing are requirements for more efficient and reliable operation, programmable controllers are part of a fundamental ecosystem, where they are responsible for collecting data and sending it to the cloud service.

The PLC410 was developed to be such controller, using the MQTT protocol as factory default, so that the manufacturing plant operation is integrated with operational data, creating operational intelligence.



### Main characteristics

- Cloud-based solution: software always up-to-date, enabling updated information in real time, anywhere.
- Optimal use of resources.
- Reduced machine downtime and higher performance.
- Configurable and customizable dashboards and reports, with various graphic and analytical views.
- Monitoring of OEE and creation of KPIs.
- Collection, view and history of process and production data.
- Customizable anomaly alarms, which can be sent by email and SMS.
- Simplified machine location.
- Co-creation of applications.
- Integration with other platforms, such as ERP, MES.
- Creation of new business models for machine manufacturers: opportunity to sell service to end customers.
- Development of predictive maintenance and control strategies (connectivity with WEG Motor Scan).
- Monitoring of machine devices, such as sensors, PLCs, drives and operating interfaces.



For more information about **WEG Smart Machine**, please contact the Digital & Systems sales team.




# Specifications

<b>Versions</b>		PLC410
<b>Power supply</b>		24 Vdc (V min.: 20.4 Vdc / V max.: 28.8 Vdc)
		Power supply: minimum recommended capacity 2 A
		CPU consumption in normal operation: 75 mA (without accessories and without active communication networks). This value may vary due to the CPU mounting plus expansion boards.
<b>Processor</b>		Dual Core @400 MHz + coprocessor @200 MHz
<b>Scan cycle time</b>	100 thousand instructions	Total time: 1.6ms
	Per instruction	0.0162 µs
<b>Memory</b>	RAM	256 MB
	Flash	4 GB
	Data	4 MB
	Code	8 MB
	Retentive	64 kB
	Persistent	16 kB
<b>Maximum instruction capacity</b>		Approximately 6 million simple instructions
<b>Digital inputs</b>		8 DI x PNP
		Fast inputs: DI1 to DI4 - 150 kHz per channel
		Maximum input voltage 28.8 V
		High level: Vin ≥ 10 Vdc
		Low level: Vin ≤ 5 Vdc
		Consumption @ 24 Vdc: 2.1 mA
		Insulation voltage: 500 V
<b>Digital outputs</b>		Max. number of DIs via expansion boards: 200 points + remote units via Fieldbus
		8 DO (DO1...DO3 – Push-Pull / DO4...DO8 – PNP)
		Recommended voltage V+: 24 Vdc
		Maximum voltage V+: 28.8 Vdc
		Maximum frequency of PWM outputs (DO1, DO2 and DO3): 300 kHz
		Maximum current of outputs DO1...DO3: 100 mA/output
		Maximum current of outputs DO4...DO8: 500 mA/output
<b>Communication ports</b>		Max. number of DOs via expansion boards: 200 points + remote units via Fieldbus
		Serial CAN
		Serial RS485
		Ethernet
		Mini USB device
		USB host
<b>MicroSD card</b>		Max.: 2 TB (optional accessory: 8 GB card code: 16352814)
<b>Maximum number of expansion boards</b>		8 <sup>1)</sup>
<b>Software</b>		CODESYS® (V 3.5 SP19 or later – free)
<b>Cloud solutions</b>		WEG Smart Machine - WEGnology
<b>Programming language</b>		LD (ladder) – ST (structured text) – IL (instruction list) - SFC (sequential function chart) – FBD (function block diagram)
<b>Operating temperature</b>		0 °C ~ 50 °C (32 °F ~ 122 °F)
<b>Storage temperature</b>		-25 °C ~ 60 °C (-13 °F ~ 140 °F)
<b>Protection rating</b>		IP20
<b>Pollution degree</b>		2 (according to EN 50178 and UL 508C), with non-conductive pollution.
<b>Altitude</b>		1,000 m (3,300 ft). Above 1,000 m up to 4,000 m (3,300 ft to 13,200 ft), the output current must be derated by 1% for every 100 m (328 ft)
<b>Mounting</b>		On DIN rail or on panel with screws
<b>Certifications</b>		UL / CE / UKCA
<b>Dimensions (H x W x D)</b>		131.7 x 110.7 x 99 mm (5.18 x 4.35 x 3.89 in)
<b>Weight</b>		0.350 kg (0.771 lbs)

Notes: 1) For further information on mounting limitations, refer to the product user manual (chapter 13 - Expansion Modules).  
2) MicroSD card not included.

# Dimensions

Dimension reference	A	B	C	D	E	F	G	H	I
Dimension in mm (in)	101.7 (4)	115 (4.53)	110.7 (4.36)	20.6 (0.81)	84.7 (3.33)	35.8 (1.41)	115 (4.53)	101.7 (4)	89.5 (3.52)
Fixing screw	M3 Ø 3.1 (0.122)								



# Simple and quick expansion module installation

## Connection of the expansion module

Connecting the expansion modules is quick and simple:

- 1** Remove the module cover.
- 2** Add the expansion module by sliding it in until it is fully aligned with the back.
- 3** Attach to cover to the last expansion module.



## Specifications

The user easily and quickly installs the expansion boards on the PLC410 through the Plug & Play concept. When the PLC410 is powered up, the electronic circuit identifies the number of connected expansions, the model and the firmware version of each one. They also receive an address according to their position so that it is possible to access them through the communication bus.

### Expansion units

Reference	Internal current consumption <sup>1)</sup> (mA)	Inputs					Outputs		
		Bidirectional digital	Voltage or current analog	J, K and T type thermocouple	RTD Pt100/ Pt1000	Load cells	Isolated PNP digital (500 mA)	Voltage (0 – 10 V) or current (0 – 20 mA) analog	Voltage analog (0 – 10 V)
MOD1.00-24DI	0	24	-	-	-	-	-	-	-
MOD1.10-24DO	0	-	-	-	-	-	24	-	-
MOD1.20-16DO8DI	0	8	-	-	-	-	16	-	-
MOD1.30-8DO16DI	0	16	-	-	-	-	8	-	-
MOD2.00-7AI	40	-	7	-	-	-	-	-	-
MOD3.00-8AOVI	150	-	-	-	-	-	-	4	4
MOD4.00-7TH	0	-	-	7	-	-	-	-	-
MOD5.00-4RTD	0	-	-	-	4	-	-	-	-
MOD6.00-2SG	30	-	-	-	-	2	-	-	-

Note: 1) The sum of internal current consumption of MOD modules is limited to 300 mA and with a maximum number of 8 modules per PLC410. If this value is exceeded, an error will be generated in the CODESYS® programming software.

# Technical characteristics


General technical characteristics		
Digital inputs	Type	Bidirectional
	Maximum input voltage	+28.8 V
	Voltage levels for detection	High level: $V_{in} \geq 10\text{ V}$ / Low level: $V_{in} \leq 3\text{ V}$
	Consumption	24 V: 10 mA
	Insulation voltage	500 V
Analog inputs	Type	Current or voltage input
	Voltage range	0 to 10 V differential
	Common mode voltage limits	-10 to 10 V
	Current range	0 to 20 mA
	Resolution	24 Bits
Digital outputs	Type	PNP
	Recommended voltage	+24 V
	Maximum voltage	+28 V
	Maximum current per output	500 mA
Current analog outputs	Maximum current	20 mA
	Maximum load	500 $\Omega$
	Resolution	16 Bits
Thermocouple inputs	Type	J, K and T
RTD input	Type	Pt100 and Pt1000 with 2 or three wires <sup>1)</sup>
Load cell input	Type	4 or 6 wires
Relay output	Type	Isolated outputs
	Maximum load	7 A - 250 V <sub>ac</sub> , resistive load / 5 A - 30 V <sub>dc</sub> , resistive load
Operating temperature		0 °C to 45 °C
Air relative humidity		Air relative humidity: 5% to 90% non-condensing
Protection rating		IP20
Pollution degree		2 (according to EN 50178 and UL 508C), with non-conductive pollution
Altitude		1,000 m (3,300 ft). Above 1,000 m up to 4,000 m (3,300 ft to 13,200 ft), the output current must be derated by 1% for every 100 m (328 ft) above 1,000 m (3,300 ft)

Note: 1) A three-wire model is required to perform the wire resistance compensation.

## Dimensions

### Expansions

Dimension reference	A	B	C	D	E	F	G	H	I	J
Dimension in mm (in)	115.7 (4.56)	25 (0.98)	19 (0.74)	123.1 (4.84)	19 (0.74)	117.1 (4.61)	35.5 (1.4)	57.9 (2.28)	89.4 (3.52)	31.6 (1.25)
Fixing screw	M3 Ø 3.1 (0.122)									





# Global presence is essential, as much as understanding your needs.



## Global Presence

With more than 47,000 employees worldwide, WEG is one of the largest electric motors, electronic equipments and systems manufacturers. We are constantly expanding our portfolio of products and services with expertise and market knowledge. We create integrated and customized solutions ranging from innovative products to complete after-sales service.

WEG's know-how guarantees the **PLC – PLC410 Programmable Logic Controller** is the right choice for your application and business, assuring safety, efficiency and reliability.





**Availability** is having a global support network



**Partnership** is creating solutions that suits your needs



**Competitiveness** is combining technology and innovation



# Learn More

High performance and reliable products to improve your production process.



Excellence is to provide a whole solution in industrial automation that improves our customers productivity.

Visit: [www.weg.net](http://www.weg.net)

 [youtube.com/wegvideos](https://youtube.com/wegvideos)

The scope of WEG Group solutions is not limited to products and solutions presented in this catalogue.

**To see our portfolio, contact us.**

**For WEG's worldwide operations visit our website**



**[www.weg.net](http://www.weg.net)**



 1-800-ASK-4WEG

 [wec-automationsales@weg.net](mailto:wec-automationsales@weg.net)

 Duluth, GA, USA

50161419 | Rev: 00 | Date (m/y): 11/2025

The values shown are subject to change without prior notice.  
The information contained is reference values.